







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2012-12-06	Fisher	Initial Release
B	LEN1310204	2013-02-20	Fisher	Change Plating and PCB Layout
C	LE313C0104	2013-12-16	Fisher	Change Plating and Dimensions



RECOMMENDED P.C.B. LAYOUT
GENERAL TOLERANCE IS ±0.05

- Notes:
- * Important Dimension To Check.
 - * Housing: High temperature thermoplastic. UL94V-0, color is Natural white.
 - * Terminal: Copper Alloy, Gold Plated on contact area. Tin plated on solder tails.
 - * Solder Peg: Copper Alloy, Tin plated over Nickel.

UNIT: mm		TITLE SSL-1.1 DC JACK CONNECTOR 2-POS. WITH POST, SMT TYPE		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO SSL11-J2C00-000001	DRAWN BY Fisher_Wang	DATE 2013-12-16
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 6:1	SIZE A4	SHEET 1 OF 2		DWG NO SSL11-J2C00-000001	CHECKED BY Ivan_Lin	DATE 2013-12-16
REV. C		WC-REV. A.2	Inspection item			CUSTOMER ALTW	APPROVED BY Kevin_Hu	DATE 2013-12-16

