



NAN-P Series: Rigid PCB Antennas

<i>Image</i>	<i>Size</i>	<i>Protocol</i>	<i>Frequency</i>	<i>Coverage</i>	<i>NIC PN</i>
	35 mm x 7 mm	ISM / LoRa	863 ~ 870 MHz	Single Band	NAN-P868SBAX100AF
	35 mm x 7 mm	ISM / LoRa	902 ~ 928 MHz	Single Band	NAN-P915SBAX100AF
	38.6 mm x 6 mm	WIFI	2400 ~ 2483 MHz	Single Band	NAN-P2450SBAX100AF
	30 mm x 5 mm	WIFI	2400 ~ 2484MHz	Single Band	NAN-P2442SBAX96AF
	25 mm x 7 mm	WIFI	2400 ~ 2500 MHz 4900 ~ 5900 MHz	Dual Band	NAN-P2442-5400DBAX100AF
	36 mm x 14 mm	WIFI	2400 ~ 2483.5 MHz 4900 ~ 5825 MHz	Dual Band	NAN-P2450-5400DBBX100AF
	45 mm x 7 mm	WIFI	2400 ~ 2483.5 MHz 4900 ~ 5825 MHz	Dual Band	NAN-P2450-5400DBAX100BF
	40 mm x 15 mm	LTE	698 ~ 960 MHz 1710 ~ 2690 MHz	Dual Band	NAN-P829-2200DBAX100AF