

Coaxial Cable Connector 11_QMA-W50-2-8/133_N

Description

Straight cable plug

Interface standards

QMA IP 68 rated - QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0047 kg

Environmental Data

Operating temperature	-40 °C to 105 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00119158
Catalogue drawing	DCA-00200073
Assembly instruction	DOC-0000312675

Ordering Information

Bulk 100 pcs package	11_QMA-W50-2-8/133_NH
----------------------	-----------------------

Additional Information

Suitable cables	ENVIROFLEX_316, RG_174_/U, RG_316_/U
-----------------	--------------------------------------