



Pushing Performance
Since 1945

Han-INOX® 24B-C-f. DL



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 024 5405
Specification	Han-INOX® 24B-C-f. DL
HARTING eCatalogue	https://b2b.harting.com/19440245405

Identification

Category	Accessories
Series of hoods/housings	Han-INOX®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings Metal With fixing cord (cable shoe)

Version

Size	24 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	181.4 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140829435
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors