






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-710076	2006/12/18	DongYaLi	Move O-Ring To ZSE00100714
C	LEN1390189	2013/09/02	Lu Di	Update Dimension




With Liquid Glue
點防水膠



Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為 1.2mm以下


Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚為 1.2~2.0mm

- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate : IP68
IP68: 1M of depth of water 24 hours
(防水等級 : IP68)
(IP68: 1米水深24小時)
 - * Do Mating Test After Glued
點膠後, 須作對插測試
 - * HD-SUB Conn. : Black Core, PBT
 - * Plastic Jacket : Black, Nylon+GF
 - * Pin: Copper Alloy, Gold Plated
 - * Ring: Light Blue, Silicone
 - * Screw: Copper Alloy, Nickel Plated, #4-40 UNC
 - * HD-SUB Conn. : Black Core, PBT
 - * The 90° Board Lock Needs To Connect The Iron Shell
L型支架需接鐵殼



15 Pin Female Conn.
PCB Pin Layout

Max. Distance From The
Circuit Board Edge
距離 PCB 板邊尺寸



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT: mm		TITLE HDI5/F Conn, Panel, PCB 90° Add Board Lock		Amphenol LTW		ITEM NO HDB-15PFFP-SB8001	DRAWN BY Di_lu	DATE 2013/09/02
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 1:1	SIZE A4	安費諾亮泰企業股份有限公司		DWG NO HDB-15PFFP-SB8001	CHECKED BY Mafei	DATE 2013/09/02
REV. C		WC-REV. A.3	SHEET 1 OF 1		CUSTOMER ALTW		APPROVED BY Victor	DATE 2013/09/02