

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

B

PRODUCT NUMBER
85853-XYX OR 85853-XYXX
85853-XYXLF OR 85853-XYXXLF



A


B

mat'l code				--				tolerances unless otherwise specified				CUSTOMER				A FCI www.fciconnect.com									
lfr	ecn no.	dr	date	linear	0.X ±0.3				COPY				projection MM scale 2:1				title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT								
CN	V03-1321	DAI	01/15/04		0.XX ±0.13																				
CP	V04-0063	HTB	01/20/04		.XXX ±.051																				
CR	V04-0151	HTB	02/13/04	angles	0° ±2°								product family				METRAL				code				
CS	V04-0408	TAB	04/27/04	dr	T.BRUNGARD 11/19/99								size		dwg no				213						
CT	V04-0353	DAI	05/02/04	enrg	M.STRAWSER 11/19/99								A		85853				sheet 1 of 1						
CU	V04-0559	HTB	06/01/04	chr	M.STRAWSER 11/19/99																				
CV	V04-1100	DAI	01/25/05	appd	M.STRAWSER 02/29/00																				
sheet index		revision		CV	CV	CV	CV	CV	CV	CV	CV	CV	CV	CV	CV	CV	CV	CV	CV						
		sheet		1	2	3		4	5	6	7		8	9	10		11	12	13	14	15				
Pro/E								3								cage code				22526				4	

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
25	5.75	15.60
33	7.25	12.90
36	5.75	14.40
49	5.75	15.10
64	5.75	14.90
67	7.25	16.30

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com		
lfr	ecr no.	dr	date	linear	0. X ± 0.3		COPY			title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT		
CV			0. XX ± 0.13		projection							
			. XXX ± .051									
				angles	0° ± 2°							
				dr	T. BRUNGARD	11/19/99	MM scale 1 : 1		product family		METRAL	code
				enr	M. STRAWSER	11/19/99			size	dwg no	213	
				chr	M. STRAWSER	11/19/99			85853		sheet	
				appd	M. STRAWSER	02/29/00					2	
sheet index	revision sheet											

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

A

FCI

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X01 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X02 SEE NOTE 10 LEAD FREE OPTION	E	3	3	19	3	19	3	19	3	19	3
	D	3	19	3	3	19	3	3	19	3	3
	C	19	3	3	19	3	3	19	3	3	19
	B	3	3	19	3	3	19	3	3	19	3
	A	3	19	3	3	19	3	3	19	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X03 SEE NOTE 10 LEAD FREE OPTION	E	19	3	19	3	19	3	19	3	19	3
	D	3	19	3	19	3	19	3	19	3	19
	C	19	3	19	3	19	3	19	3	19	3
	B	3	19	3	19	3	19	3	19	3	19
	A	19	3	19	3	19	3	19	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X04 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10	10	10	10	10
	D	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X05 SEE NOTE 10 LEAD FREE OPTION	E	7	6	5	5	5	5	5	5	5	5
	D	7	6	5	5	5	5	5	5	5	5
	C	7	6	5	5	5	5	5	5	5	5
	B	7	6	5	5	5	5	5	5	5	5
	A	7	6	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X06 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X07 SEE NOTE 10 LEAD FREE OPTION	E	33	7	7	7	7	7	7	7	7	7
	D	36	7	7	7	7	7	7	7	7	7
	C	33	7	7	7	7	7	7	7	7	7
	B	36	7	7	7	7	7	7	7	7	7
	A	33	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X08 SEE NOTE 10 LEAD FREE OPTION	E	4	1	1	1	19	1	1	1	1	1
	D	3	1	1	1	19	1	1	1	1	1
	C	3	1	1	1	19	1	1	1	19	1
	B	3	1	1	1	19	1	1	1	19	1
	A	3	1	1	1	19	1	1	1	19	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X09 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4
	B	1	2	2	2	2	2	2	1	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X10 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	20
	D	6	6	6	6	6	6	6	6	6	20
	C	6	6	6	6	6	6	6	6	6	20
	B	6	6	6	6	6	6	6	6	6	20
	A	6	6	6	6	6	6	6	6	6	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X11 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	4	2	19
	D	2	2	2	2	2	4	2	4	2	19
	C	2	2	2	2	2	4	2	4	2	19
	B	2	2	2	2	2	4	2	4	2	19
	A	2	2	2	2	2	4	2	4	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X12 SEE NOTE 10 LEAD FREE OPTION	E	8	8	8	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	20	20	20	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	8	8	8	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X13 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	19	19	19	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	4	4	4	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com				
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD. 5 ROW PRESS-FIT				
CV					0.XX ±0.13	projection						
					.XXX ±0.051							
				angles	0° ±2°			product family METRAL				
				dr	T.BRUNGARD					11/19/99	code 213	
				enrg	M.STRAWSE					11/19/99		
				chr	M.STRAWSE	11/19/99	size A					
				appd	M.STRAWSE	02/29/00			dwg no 85853			
sheet	revision										sheet 3	
index	sheet											

A

B

1 | 2

3 |

4

1 | 2

Pro/E

3 |

cage code
22526

4

PDM: Rev:CV

STATUS: **Released**

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X14 SEE NOTE 10 LEAD FREE OPTION	E	1	4	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	4	1	4	3	1
	C	1	1	1	4	1	1	1	4	3	1
	B	1	4	1	1	1	1	1	4	3	1
	A	1	1	1	1	1	4	1	4	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X15 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	4	1	1	1	4	1	1
	D	1	4	1	1	1	1	4	1	1	4
	C	1	1	1	1	4	1	1	1	4	1
	B	1	1	4	1	1	1	1	4	1	1
	A	1	1	1	1	1	4	1	1	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X16 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	3	3	1	1	1
	D	1	1	1	1	1	3	3	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X17 SEE NOTE 10 LEAD FREE OPTION	E	1	4	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	4	1	4	3	1
	C	1	1	1	4	1	1	1	4	3	1
	B	1	4	1	1	1	1	1	4	3	1
	A	1	1	1	1	1	4	1	4	3	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X18 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	4	1	1	1	4	1	1
	D	1	4	1	1	1	1	1	4	1	1
	C	1	1	1	1	4	1	1	1	4	1
	B	1	1	4	1	1	1	1	4	1	1
	A	4	4	1	1	1	4	1	1	1	4

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X19 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25
	A	25	25	25	25	25	25	25	25	25	25

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X20 SEE NOTE 10 LEAD FREE OPTION	E	3	2	2	2	2	2	3	2	2	2
	D	3	2	2	2	2	2	2	2	2	3
	C	3	2	2	2	4	4	4	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X21 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	19
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	2	2	2	2	4	2	4	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X22 SEE NOTE 10 LEAD FREE OPTION	E	4	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	19	19	19	2	2	19	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	2
	A	4	2	2	2	2	4	2	2	2	2

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X23 SEE NOTE 10 LEAD FREE OPTION	E	49	49	49	49	49	49	49	49	49	49
	D	49	49	49	49	49	49	49	49	49	49
	C	49	49	49	49	49	49	49	49	49	49
	B	49	49	49	49	49	49	49	49	49	49
	A	49	49	49	49	49	49	49	49	49	49

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X24 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	20
	D	6	6	6	6	6	6	6	6	6	20
	C	6	6	6	6	6	6	6	6	6	20
	B	6	6	6	6	6	6	6	6	6	20
	A	6	6	6	6	6	8	6	8	6	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X25 SEE NOTE 10 LEAD FREE OPTION	E	8	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	20	20	20	6	6	20	6	6	6	6
	B	6	6	6	6	6	8	6	6	6	6
	A	8	6	6	6	6	8	6	6	6	6

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X26 SEE NOTE 10 LEAD FREE OPTION	E	1	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

B

mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com				
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD. 5 ROW PRESS-FIT				
CV					0.XX ±0.13	projection						
					.XXX ±.051							
				angles	0° ±2°			product family METRAL				
				dr	T.BRUNGARD					11/19/99	code 213	
				enr	M.STRAWSER					11/19/99		
				chr	M.STRAWSER	11/19/99	size A					
				appd	M.STRAWSER	02/29/00			dwg no 85853			
sheet	revision										sheet 4	
index	sheet											

1 | 2

Pro/E

3 |

cage code
22526

4

PDM: Rev:CV

STATUS: **Released**

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers
interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

A
FCI

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X27 SEE NOTE 10 LEAD FREE OPTION	E	5	7	7	7	7	7	7	7	7	7
	D	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X28 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	-	2	-	-
	D	2	2	2	2	2	2	-	-	-	-
	C	2	2	2	2	2	2	2	2	-	-
	B	2	2	2	2	2	2	-	-	-	-
	A	2	2	2	2	2	2	-	2	-	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X29 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-
	D	-	-	-	-	-	-	-	-	-	-
	C	2	-	2	-	2	-	2	-	2	-
	B	-	-	-	-	-	-	-	-	-	-
	A	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X30 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	3	3	19	19
	D	-	-	-	-	-	-	3	3	19	19
	C	2	-	2	-	2	-	3	3	19	19
	B	-	-	-	-	-	-	3	3	19	19
	A	2	-	2	-	2	-	3	3	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X31 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	4	2	2	2
	D	-	-	-	-	-	-	4	2	2	2
	C	2	-	2	-	2	-	4	2	2	2
	B	-	-	-	-	-	-	4	2	2	2
	A	2	-	2	-	2	-	4	2	2	2

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X32 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	20	7	7	7	6
	D	20	7	7	7	7	20	7	7	7	6
	C	20	7	7	7	7	20	7	7	7	6
	B	20	7	7	7	7	20	7	7	7	6
	A	20	7	7	7	7	20	7	7	7	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X33 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	20	7	7	7	7
	D	20	7	7	7	7	20	7	7	7	7
	C	20	7	7	7	7	20	7	7	7	7
	B	20	7	7	7	7	20	7	7	7	7
	A	20	7	7	7	7	20	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X34 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	2	2	2
	D	-	-	-	-	-	-	2	2	2	2
	C	2	-	2	-	2	-	2	2	2	2
	B	-	-	-	-	-	-	2	2	2	2
	A	2	-	2	-	2	-	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X35 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	2
	D	19	3	3	3	3	3	19	3	3	2
	C	19	3	3	3	3	3	19	3	3	2
	B	19	3	3	3	3	3	19	3	3	2
	A	19	3	3	3	3	3	19	3	3	2

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X36 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	3
	D	19	3	3	3	3	3	19	3	3	3
	C	19	3	3	3	3	3	19	3	3	3
	B	19	3	3	3	3	3	19	3	3	3
	A	19	3	3	3	3	3	19	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X37 SEE NOTE 10 LEAD FREE OPTION	E	1	-	1	-	1	-	1	-	1	-
	D	-	1	-	1	-	1	-	1	-	1
	C	1	-	1	-	1	-	1	-	1	-
	B	-	1	-	1	-	1	-	1	-	1
	A	1	-	1	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X38 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	-	19	-	19	-	19
	D	19	19	19	19	-	19	-	19	-	19
	C	19	19	19	19	-	19	-	19	-	19
	B	19	19	19	19	-	19	-	19	-	19
	A	19	19	19	19	-	19	-	19	-	19

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X39 SEE NOTE 10 LEAD FREE OPTION	E	3	3	7	3	3	7	7	7	7	7
	D	3	3	7	3	3	7	7	7	7	7
	C	3	7	7	7	3	7	7	7	7	7
	B	3	3	3	3	3	7	7	7	7	7
	A	3	3	3	3	3	3	3	3	3	3

B

1 | 2

Pro/E

3 |

cage code 22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

mat'l code				tolerances unless otherwise specified				CUSTOMER		A FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3				COPY		title METRAL SIGNAL HEADER 2 MOD. 5 ROW PRESS-FIT
CV					0.XX ±0.13				projection		
					.XXX ±.051						
				angles	0° ±2°						product family METRAL
				dr	T.BRUNGARD		11/19/99		MM scale 1:1		
				enrg	M.STRAWSER		11/19/99				
				chr	M.STRAWSER		11/19/99				
				appd	M.STRAWSER		02/29/00				
sheet		revision								code 213	
index		sheet								sheet 5	

B

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X40 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	4	4	4	4	4	4	4
	D	4	4	4	4	4	4	4	4	4	4
	C	4	4	4	4	4	4	4	4	4	1
	B	4	4	4	4	4	4	4	4	4	4
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X41 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	-	3	3	-	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X42 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	1	1	1	1
	D	2	2	2	2	2	1	1	1	1	1
	C	1	1	1	1	1	2	2	2	2	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X43 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	5	5	5	5	5
	D	2	2	2	2	2	5	5	5	5	5
	C	1	1	1	1	1	6	6	6	6	5
	B	1	1	1	1	1	5	5	5	5	5
	A	1	1	1	1	1	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X44 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	5	5	5	5	5
	D	6	6	6	6	6	5	5	5	5	5
	C	5	5	5	5	5	6	6	6	6	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

1 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X45 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	5	5	6	6	6	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X46 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	1	2	2	2	2	2
	D	2	2	2	2	1	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X47 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	-
	D	-	5	5	-	5	5	-	5	5	-
	C	-	5	5	-	5	5	-	5	5	-
	B	-	5	5	-	5	5	-	5	5	-
	A	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X48 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	3	2	2	2	2
	D	2	2	2	2	2	3	2	2	2	2
	C	2	2	2	2	2	3	2	2	2	2
	B	2	2	2	2	2	3	2	2	2	2
	A	2	2	2	2	2	3	2	2	2	3

3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X49 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	2	2	2	2
	D	1	1	1	1	1	1	2	2	2	2
	C	1	1	2	2	2	2	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X50 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	2	2	2	2
	D	5	5	5	5	5	5	2	2	2	2
	C	5	5	6	6	6	6	1	1	1	1
	B	5	5	5	5	5	5	1	1	1	1
	A	5	5	5	5	5	5	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X51 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	6	6	6	6
	D	5	5	5	5	5	5	6	6	6	6
	C	5	5	6	6	6	6	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X52 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	19	19	19	1
	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	19	19	19	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	19	19	19	1

B

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3		COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT
CV					0.XX ±0.13		projection		
					.XXX ±.051				
				angles	0° ±2°				product family METRAL
					dr		T.BRUNGARD 11/19/99		
					enrg		M.STRAWSER 11/19/99		
					chr		M.STRAWSER 11/19/99		code 213
					appd		M.STRAWSER 02/29/00		
sheet		revision							
index		sheet							

Pro/E

3

cage code 22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A
FCI

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X53 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	1
	D	-	1	1	-	-	-	-	-	-	1
	C	-	-	-	-	-	-	-	-	-	-
	B	-	1	1	-	-	1	-	1	1	-
	A	-	1	1	-	-	1	-	1	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X54 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	-	1	-	1	-	-
	D	1	1	1	1	-	1	-	1	-	-
	C	1	1	1	1	-	1	-	1	-	-
	B	1	1	1	1	-	1	-	1	-	-
	A	1	1	1	1	-	1	-	1	-	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X55 SEE NOTE 10 LEAD FREE OPTION	E	2	19	19	19	19	19	19	19	19	19
	D	2	19	19	19	19	19	19	19	19	19
	C	2	19	19	19	19	19	19	19	19	19
	B	2	19	19	19	19	19	19	19	19	19
	A	2	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X56 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	-	19	-	19	-	-
	D	19	19	19	19	-	19	-	19	-	-
	C	19	19	19	19	-	19	-	19	-	-
	B	19	19	19	19	-	19	-	19	-	-
	A	19	19	19	19	-	19	-	19	-	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X57 SEE NOTE 10 LEAD FREE OPTION	E	-	19	-	-	19	-	19	-	19	19
	D	-	19	-	-	19	-	19	-	19	19
	C	-	19	-	-	19	-	19	-	19	19
	B	-	19	-	-	19	-	19	-	19	19
	A	-	19	-	-	19	-	19	-	19	19

1 | 2

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X58 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	1
	D	-	1	1	-	-	-	-	-	-	1
	C	-	-	-	-	-	-	-	-	-	-
	B	-	1	1	-	1	1	-	1	1	-
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X59 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	3	3	3	3	3	3
	D	3	-	3	3	3	3	3	3	3	3
	C	-	-	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X60 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	19	-	19	-	2	-	19
	D	2	2	2	19	-	19	-	2	-	19
	C	2	2	2	19	-	19	-	2	-	19
	B	2	2	2	19	-	19	-	2	-	19
	A	2	2	2	19	-	19	-	2	-	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X61 SEE NOTE 10 LEAD FREE OPTION	E	19	2	2	2	2	2	2	2	2	2
	D	19	2	2	2	2	2	2	2	2	2
	C	19	2	2	2	2	2	2	2	2	2
	B	19	2	2	2	2	2	2	2	2	2
	A	19	2	2	2	2	2	2	2	2	2

3 |

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X62 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	20	-	20	-	6	-	6
	D	6	6	6	20	-	20	-	6	-	6
	C	6	6	6	20	-	20	-	6	-	6
	B	6	6	6	20	-	20	-	6	-	6
	A	6	6	6	20	-	20	-	6	-	6


METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X63 SEE NOTE 10 LEAD FREE OPTION	E	20	6	6	6	6	6	6	6	6	6
	D	20	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6
	B	20	6	6	6	6	6	6	6	6	6
	A	20	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X64 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	-	-	-	2	2	-	-	-	2
	A	2	-	2	-	-	2	2	-	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X65 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5
	D	5	5	6	5	5	5	5	5	6	5
	C	5	5	6	5	5	5	5	5	6	5
	B	5	5	6	5	5	5	5	5	6	5
	A	5	5	6	5	5	5	5	5	6	5

A

B

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3		COPY			title	
CV					0.XX ±0.13		projection			METRAL SIGNAL HEADER	
					.xxx ±.051					2 MOD. 5 ROW PRESS-FIT	
				angles	0° ±2°					product family	
					dr T.BRUNGARD 11/19/99					METRAL	
					enr M.STRAWSER 11/19/99					code	
					chr M.STRAWSER 11/19/99					size	
					appd M.STRAWSER 02/29/00					dwg no	
sheet		revision								A	
index		sheet								85853	
										213	
										7	
										cage code	
										22526	

Pro/E

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

A
FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X66 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5
	D	5	5	6	5	5	5	5	5	6	5
	C	5	5	6	5	5	5	5	5	6	5
	B	5	5	6	5	5	5	5	5	6	5
	A	5	5	6	5	5	5	5	5	6	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X67 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	5	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	20	20
	B	6	6	6	6	6	6	6	6	20	6
	A	6	6	6	6	6	6	6	6	20	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X68 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	3	2
	C	2	2	2	2	2	2	2	2	3	2
	B	2	2	2	2	2	2	2	2	3	2
	A	2	2	2	2	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X69 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	4	2	2	2	2	2
	D	2	2	2	2	4	2	2	2	2	2
	C	2	2	2	2	4	4	4	4	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X70 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	2	2	2
	D	2	2	2	2	2	4	2	2	2	2
	C	2	2	2	2	2	4	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	2
	A	2	2	2	2	2	4	2	2	2	2

1 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X71 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	3	2	2	2
	D	2	2	2	2	2	2	3	2	2	2
	C	2	2	2	2	2	2	3	2	2	2
	B	-	-	-	-	2	2	3	2	2	2
	A	2	2	2	2	2	2	3	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X72 SEE NOTE 10 LEAD FREE OPTION	E	1	4	4	4	4	19	4	2	19	19
	D	1	4	4	4	4	19	4	2	19	19
	C	19	4	4	4	4	19	4	2	19	19
	B	3	4	4	4	4	19	4	2	19	19
	A	3	4	4	4	4	19	4	2	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X73 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5
	D	5	5	6	5	5	5	5	5	6	5
	C	1	1	6	1	5	5	5	5	6	5
	B	5	5	6	5	5	5	5	5	6	5
	A	5	5	6	5	5	5	5	5	6	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X74 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	3	2
	D	2	2	2	2	2	2	2	2	3	2
	C	2	2	2	2	2	2	2	2	3	2
	B	2	2	2	2	2	2	2	2	3	2
	A	2	2	2	2	2	2	2	2	2	2

3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X75 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	8	6	8	8	6	8	8	8	6
	B	6	6	6	6	8	6	6	6	6	6
	A	6	6	6	6	8	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X76 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	3	1	1	1	1
	D	1	1	1	1	1	3	1	1	1	1
	C	1	1	1	1	1	3	1	1	1	1
	B	1	1	1	1	1	3	1	1	1	1
	A	1	1	1	1	1	3	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X77 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	1	2	2	2	2	1	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X78 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	1	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

B

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com		
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD. 5 ROW PRESS-FIT		
CV					0.XX ±0.13	projection				
					.XXX ±.051					
				angles	0° ±2°			product family METRAL		
				dr	T.BRUNGARD					11/19/99
				enr	M.STRAWSER					11/19/99
				chr	M.STRAWSER	11/19/99	size		dwg no	
				appd	M.STRAWSER	02/29/00	A		85853	
sheet	revision						8		213	
index	sheet						8		8	

Pro/E

3

cage code 22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X79 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	7	5	5	5	5
	D	5	5	5	5	5	7	5	5	5	5
	C	5	5	5	5	5	7	5	5	5	5
	B	5	5	5	5	5	7	5	5	5	5
	A	5	5	5	5	5	7	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X80 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	6	5	5	5	5
	D	5	5	5	5	5	6	5	5	5	5
	C	5	6	5	6	6	6	5	5	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X81 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	5	6	6	5	6	6	5	6	5
	B	5	5	5	5	6	5	5	5	5	6
	A	5	5	5	5	6	5	5	5	5	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X82 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	-
	D	1	1	1	1	1	1	1	1	1	-
	C	1	1	1	1	1	1	1	1	1	-
	B	1	1	1	1	1	1	1	1	1	-
	A	1	1	1	1	1	1	1	1	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X83 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-
	D	-	2	-	-	-	2	-	-	2	-
	C	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	-	-	2	-	-	2	-
	A	2	-	2	-	2	-	2	-	2	-

1 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X84 SEE NOTE 10 LEAD FREE OPTION	E	-	-	4	4	4	4	4	4	4	-
	D	-	-	4	4	4	4	4	2	2	-
	C	-	-	4	2	2	4	4	4	4	-
	B	-	-	4	4	4	4	4	2	2	-
	A	-	-	4	4	4	4	4	4	4	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X85 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	2	2	2
	D	-	-	-	-	-	-	2	2	2	2
	C	2	2	2	-	2	2	-	2	2	2
	B	2	2	2	-	2	2	-	2	2	2
	A	2	2	2	-	2	2	-	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X86 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	1	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X87 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	-	1
	D	1	1	1	1	1	1	1	1	-	1
	C	1	1	1	1	1	1	1	1	-	1
	B	1	1	1	1	1	1	1	1	-	-
	A	1	1	1	1	1	1	1	1	1	1

3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X88 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	-	1	1	1
	C	1	1	1	1	1	-	-	-	-	1
	B	3	3	3	3	3	-	3	-	3	-
	A	1	1	1	1	1	1	-	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X89 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	-	3	1	1
	D	3	3	3	3	3	-	3	-	3	-
	C	1	1	1	1	1	1	-	-	-	-
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X90 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	3	3	3	3	3	3
	D	3	-	3	3	3	3	3	3	3	3
	C	-	-	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X91 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	1	3	3	3	3	3	3	3	3	1
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

B

1 2

Pro/E

3

cage code 22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY	title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT		
CV				angles	0.XX ±0.13	projection			
					.XXX ±.051		product family METRAL		
				dr	0° ±2°	MM			
				enr	T.BRUNGARD 11/19/99	scale	size A		
				chr	M.STRAWSER 11/19/99	1:1			
				appd	M.STRAWSER 02/29/00		code 213		
sheet	revision						sheet 9		
index	sheet								

A FCI

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X92 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	
	D	-	5	5	-	5	5	-	5	5	
	C	-	5	5	-	5	5	-	5	5	
	B	-	5	5	-	5	5	-	5	5	
	A	-	5	5	-	5	5	-	5	5	

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X93 SEE NOTE 10 LEAD FREE OPTION	E	8	6	6	6	6	6	6	6	6	6
	D	8	6	6	6	6	6	6	6	6	6
	C	8	6	6	6	6	6	6	6	6	6
	B	8	6	6	6	6	6	6	6	6	6
	A	8	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X94 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	4
	D	2	2	2	2	2	2	2	2	2	4
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X95 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	1	1	-	1	1	
	D	-	1	1	-	1	1	-	1	1	
	C	-	1	1	-	1	1	-	1	1	
	B	-	1	1	-	1	1	-	1	1	
	A	-	1	1	-	1	1	-	1	1	

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X96 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-
	D	-	2	-	2	-	2	-	2	-	2
	C	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	2	-	2	-	2	-	2
	A	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X97 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	1	2	2	2	2	2	2	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X98 SEE NOTE 10 LEAD FREE OPTION	E	19	1	2	2	1	2	2	2	2	19
	D	1	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	1	2	2	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X99 SEE NOTE 10 LEAD FREE OPTION	E	2	1	2	2	1	2	2	2	2	19
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19
	A	2	1	2	2	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X100 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	1	1	1	1	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

3

4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X101 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	8	20	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6


METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X102 SEE NOTE 10 LEAD FREE OPTION	E	4	4	3	4	3	4	4	4	3	4
	D	4	4	3	4	3	4	4	4	3	4
	C	4	4	4	4	4	4	4	4	4	4
	B	4	4	2	4	2	4	4	4	2	4
	A	4	4	2	4	2	4	4	4	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X103 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	4	3	4	3	4	3	3
	D	3	3	3	4	3	4	3	4	3	3
	C	3	3	3	4	2	4	2	4	3	3
	B	3	3	3	4	2	4	2	4	3	3
	A	3	3	3	4	2	4	2	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X104 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	2	3	3	3	3
	D	3	3	3	3	3	2	3	3	3	3
	C	3	3	3	3	3	2	3	3	3	3
	B	3	3	3	3	3	2	3	3	3	3
	A	3	3	3	3	3	2	3	3	3	3

A

B

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com		
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY				
CV				linear	0.XX ±0.13	projection				
				angles	.xxx ±.051		title			
					0° ±2°		METRAL SIGNAL HEADER 2 MOD. 5 ROW PRESS-FIT			
				dr	T.BRUNGARD 11/19/99	product family	METRAL		code	213
				enr	M.STRAWSER 11/19/99	size	dwg no	sheet		10
				chr	M.STRAWSER 11/19/99	scale	A		85853	
				appd	M.STRAWSER 02/29/00	1:1				
sheet	revision									
index	sheet									

Pro/E

3

cage code 22526

4

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A
FCI

A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X105 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	3	3	3	3	3	3
	D	2	2	2	3	3	3	3	3	3	3
	C	2	2	2	3	3	3	3	3	3	3
	B	2	2	2	3	3	3	3	3	3	3
	A	2	2	2	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X106 SEE NOTE 10 LEAD FREE OPTION	E	3	7	7	7	7	7	8	7	8	7
	D	3	7	7	7	7	7	8	7	8	7
	C	3	7	7	7	7	7	8	7	8	7
	B	3	7	7	7	7	7	8	7	8	7
	A	3	7	7	7	7	7	8	7	8	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X107 SEE NOTE 10 LEAD FREE OPTION	E	3	8	7	7	7	7	7	7	7	7
	D	3	8	7	7	7	7	7	7	7	7
	C	3	8	7	7	7	7	7	7	7	7
	B	3	8	7	7	7	7	7	7	7	7
	A	3	8	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X108 SEE NOTE 10 LEAD FREE OPTION	E	7	8	7	8	7	8	7	8	7	8
	D	7	8	7	8	7	8	7	8	7	8
	C	8	8	8	8	8	8	8	8	8	8
	B	6	8	6	8	6	8	6	8	6	8
	A	6	8	6	8	6	8	6	8	6	8

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X109 SEE NOTE 10 LEAD FREE OPTION	E	19	1	2	2	1	2	2	2	2	19
	D	1	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	19
	B	19	2	2	2	2	2	2	2	2	19
	A	1	1	2	2	2	2	2	2	2	19

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X110 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	-	2	-	2
	D	2	-	2	-	2	-	2	-	2	-
	C	-	2	-	2	-	2	-	2	-	2
	B	2	-	2	-	2	-	2	-	2	-
	A	-	2	-	2	-	2	-	2	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X111 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	5	5
	D	5	5	6	5	5	5	6	6	6	6
	C	6	6	6	5	5	5	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6
	A	6	6	6	6	6	6	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X112 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	2	1	1	1	1
	D	1	1	1	1	1	2	1	1	1	1
	C	1	1	2	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	2	1	1	1
	A	1	1	1	1	1	1	2	2	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X113 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	4	2	2	4	3	3	4
	C	2	2	4	2	2	4	3	3	4	3
	B	2	4	2	2	4	3	3	4	3	3
	A	2	2	2	2	2	2	2	2	2	2

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X114 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	4	3	3
	D	3	3	3	3	3	3	3	4	3	3
	C	3	3	3	3	3	3	3	4	3	3
	B	3	3	3	3	3	3	3	4	3	3
	A	3	3	3	3	3	3	3	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X115 SEE NOTE 10 LEAD FREE OPTION	E	2	2	1	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X116 SEE NOTE 10 LEAD FREE OPTION	E	6	6	7	7	6	6	6	7	7	6
	D	6	6	7	7	6	6	6	7	7	6
	C	6	6	7	7	6	6	6	7	7	6
	B	6	6	7	7	6	6	6	7	7	6
	A	6	6	7	7	6	6	6	7	7	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X117 SEE NOTE 10 LEAD FREE OPTION	E	64	-	64	-	64	-	64	-	64	-
	D	-	64	-	64	-	64	-	64	-	64
	C	64	-	64	-	64	-	64	-	64	-
	B	-	64	-	64	-	64	-	64	-	64
	A	64	-	64	-	64	-	64	-	64	-

A

mat'l code				tolerances unless otherwise specified				CUSTOMER		A FCI www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3				COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT
CV					0.XX ±0.13				projection		
					.XXX ±0.051				MM		
				angles	0° ±2°				scale		product family METRAL
				dr	T.BRUNGARD		11/19/99		size A	dwg no 85853	
				enrg	M.STRAWSE		11/19/99				
				chr	M.STRAWSE		11/19/99				
				appd	M.STRAWSE		02/29/00				code 213
sheet	revision									sheet 11	
index	sheet										

B

1 | 2

Pro/E

3 |

cage code
22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

A

FCI

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X118 SEE NOTE 10 LEAD FREE OPTION	E	6	-	6	-	6	-	6	-	6	-
	D	-	6	-	6	-	6	-	6	-	6
	C	6	-	6	-	6	-	6	-	6	-
	B	-	6	-	6	-	6	-	6	-	6
	A	6	-	6	-	6	-	6	-	6	-
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X119 SEE NOTE 10 LEAD FREE OPTION	E	4	2	2	2	2	2	2	2	2	2
	D	2	2	4	4	2	2	2	2	2	2
	C	19	2	19	2	2	19	2	2	2	2
	B	2	2	2	4	2	4	2	2	2	2
	A	4	2	2	2	2	4	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X120 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	19	2
	D	2	2	2	2	2	2	2	2	19	2
	C	2	2	2	2	2	2	2	2	19	2
	B	2	2	2	2	2	2	2	2	19	2
	A	2	2	4	4	2	4	2	4	2	4
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X121 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	8
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X122 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	3	4
	D	2	2	2	2	2	2	2	2	2	4
	C	2	2	2	2	2	2	2	4	2	2
	B	2	2	2	2	2	2	2	2	2	4
	A	2	2	2	2	2	2	2	1	2	4

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X123 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	4
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X124 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X125 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	19	19	19	19	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X126 SEE NOTE 10 LEAD FREE OPTION	E	2	6	6	6	6	6	2	2	2	2
	D	2	6	6	6	6	6	2	2	2	2
	C	2	6	6	6	6	6	2	2	2	2
	B	2	6	6	6	21	6	2	2	2	2
	A	2	6	6	6	6	6	2	2	2	2

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X127 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	19	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X128 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	3	19
	D	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	19	19	2	2
	B	2	2	2	2	2	2	2	2	19	19
	A	2	2	2	2	2	2	2	2	1	19
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X129 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	3
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X130 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	7
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6

A

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com				
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT				
CV					0.XX ±0.13	projection						
					.XXX ±0.051							
				angles	0° ±2°			product family METRAL				
				dr	T.BRUNGARD					11/19/99	code 213	
				enr	M.STRAWSER					11/19/99		
				chr	M.STRAWSER	11/19/99	sheet 12					
				appd	M.STRAWSER	02/29/00						
sheet	revision								cage code 22526			
index	sheet											

B

1 | 2

Pro/E

3 |

cage code
22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

A

FCI

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X131 SEE NOTE 10 LEAD FREE OPTION	E	9	-	9	-	9	-	9	-	9	-
	D	9	-	9	-	9	-	9	-	9	-
	C	-	-	-	-	-	-	-	-	-	-
	B	9	-	9	-	9	-	9	-	9	-
	A	9	-	9	-	9	-	9	-	9	-
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X132 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6
	A	5	5	5	5	5	5	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X133 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X134 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	1	2	2	3
	D	2	2	2	2	2	1	1	2	2	3
	C	2	2	2	2	2	1	1	2	2	3
	B	2	2	2	2	2	1	1	2	2	3
	A	2	2	2	2	2	1	1	2	2	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X135 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	1	1	1	1
	D	2	2	2	2	2	1	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	1	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X136 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X137 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	-	-	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X138 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	2	2	2	3	2	2
	D	2	2	2	3	2	2	2	3	2	2
	C	2	2	2	2	3	2	2	2	3	2
	B	2	2	2	2	2	3	2	2	3	2
	A	2	2	2	2	1	2	2	2	3	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X139 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	19	19

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X140 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	4	2	2	2	2	2	4	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X141 SEE NOTE 10 LEAD FREE OPTION	E	64	64	64	64	64	64	64	64	64	64
	D	64	64	64	64	64	64	64	64	64	64
	C	67	64	64	64	64	64	67	64	64	64
	B	64	64	64	64	64	64	64	64	64	64
	A	64	64	64	64	64	64	64	64	64	64
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X142 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	1	1
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
85853-X143 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	1
	C	2	2	2	2	2	2	2	2	2	1
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

A

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com				
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT				
CV					0.XX ±0.13	projection						
					.XXX ±.051							
				angles	0° ±2°			product family METRAL				
				dr	T.BRUNGARD					11/19/99	size A	
				enr	M.STRAWSE					11/19/99		
				chr	M.STRAWSE	11/19/99	sheet 13					
				appd	M.STRAWSE	02/29/00			cage code 22526			
sheet	revision										4	
index	sheet											

B

1 | 2

Pro/E

3 |

cage code
22526

4

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


A

A

FCI

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X144 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	2	2	2	2	2	2
	D	2	2	2	2	2	1	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	1	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X145 SEE NOTE 10 LEAD FREE OPTION	E	7	6	6	6	6	6	6	6	6	6	6	6
	D	7	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6	6	6
	A	7	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X146 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	7	6	6	6	6	5	5	5	5	5	5	5
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X147 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	5	6	6	6	6
	D	6	6	6	6	6	6	6	5	6	5	6	6
	C	6	6	6	6	6	6	6	5	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	5

mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3	COPY			
CV					0.XX ±0.13	projection			
					.XXX ±.051				
				angles	0° ±2°				
				dr	T.BRUNGARD 11/19/99				
				enr	M.STRAWSER 11/19/99				
				chr	M.STRAWSER 11/19/99			scale 1:1	
				appd	M.STRAWSER 02/29/00				
sheet index		revision sheet							
								cage code 22526	

Pro/E

3

PDM: Rev:CV

STATUS:Released

Printed: Feb 10, 2006

B


PRODUCT NUMBER
85853-XYX OR 85853-XXXX
85853-XYXLF OR 85853-XXXXLF

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
85853-XYX IS SnPb
85853-XYXLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 85853-X01LF

PLATING IN CONTACT AREA		NOTES
DASH NUMBER	PERFORMANCE LEVEL	-
-PYY OR -PYXX	0.25 um GOLD MIN.	-
-N1YY OR -N1YYY	TELCORDIA CO (NXT)	-
-N5YY OR N5YYY	TELCORDIA UE (NXT)	-
-1YY OR -1YYY	TELCORDIA CO	-
-2YY OR -2YYY	TELECOM CLASS	-
-3YY OR -3YYY	IEC CLASS I	-
-5YY OR -5YYY	TELCORDIA UE	-
-9YY OR -9YYY	TELCORDIA CO	-
-N1YYLF OR -N1YYYLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-N5YYLF OR N5YYYLF	TELCORDIA UE (NXT)	SEE NOTE 9
-1YYLF OR -1YYYLF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YYLF OR -2YYYLF	TELECOM CLASS	SEE NOTE 9
-5YYLF OR -5YYYLF	TELCORDIA UE	SEE NOTE 9

mat'l code				tolerances unless otherwise specified		CUSTOMER		A FCI www.fciconnect.com				
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT				
CV					0.XX ±0.13	projection						
					.XXX ±.051							
				angles	0° ±2°	 MM		product family		METRAL	code	
				dr	T.BRUNGARD			11/19/99	size	dwg no	85853	213
				enrg	M.STRAWSE			11/19/99				
				chr	M.STRAWSE			11/19/99				
				appd	M.STRAWSE	02/29/00	scale	1:1	sheet			
sheet index		revision sheet										