



CONNECTORS
DIMM



☒ Preliminary

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**

TE CONNECTIVITY (TE)

DDR4 DIMM 288 PIN SMT TYPE

[DDR4 DIMM](#) | [DDR4 DIMM](#)

9-2199155-1

TE Internal Number: 9-2199155-1

[Not Yet Reviewed for EU RoHS](#)

[Not Yet Reviewed for EU ELV](#)

DRAM Type **Double Data Rate (DDR) 4**

Number of Positions **288**

PCB Mounting Style **Surface Mount**

Module Orientation **Vertical**

Centerline **.85 mm [.0334 in]**

Product Drawings

[DDR4 DIMM 288 Pin SMT Type](#)

PDF
English

CAD Files

[3D PDF](#)

PDF
3D

[Customer View Model](#)

2D_DXF.ZIP
English

[Customer View Model](#)

3D_IGS.ZIP
English

[Customer View Model](#)

3D_STP.ZIP
English

Product Specifications

Product Specification

[PRODUCT SPECIFICATION FOR DDR4 SMT MEMORY SOCKET](#)

PDF
English

Qualification Test Report

[Qualification Test Report For DDR4 SMT MEMORY SOCKET](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

DRAM Type

Double Data Rate (DDR) 4

Configuration Features	Number of Positions	288
	Module Orientation	Vertical
<hr/>		
Body Features	Ejector Type	Standard
<hr/>		
Mechanical Attachment	PCB Mounting Style	Surface Mount
<hr/>		
Housing Features	Centerline	.85 mm [.0334 in]
<hr/>		
Packaging Features	Packaging Method	Hard Tray
<hr/>		
Statement of Compliance	Statement of Compliance PDF	
<hr/>		