

Han TC300 male contact 70mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 7535
Specification	Han TC300 male contact 70mm ²
HARTING eCatalogue	https://b2b.harting.com/09110007535

Identification

Category	Contacts
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	70 mm ²
Rated current	≤300 A
Contact resistance	≤0.3 mΩ
Stripping length	24 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	2
Net weight	37.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188389
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors