



RELIABILITY REPORT
FOR MAX1789EUI+
PLASTIC ENCAPSULATED DEVICES

May 28, 2010

MAXIM INTEGRATED PRODUCTS

120 SAN GABRIEL DR.
SUNNYVALE, CA 94086

Approved by
Richard Aburano
Quality Assurance
Manager, Reliability Operations

Conclusion

The MAX1789EUI+ successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

Table of Contents

I.Device Description	V.Quality Assurance Information
II.Manufacturing Information	VI.Reliability Evaluation
III.Packaging Information	IV.Die Information
.....Attachments	

I. Device Description

A. General

The MAX1789 smart battery-pack controller integrates a user-programmable microcontroller core, a coulomb-counting fuel gauge, a multichannel data-acquisition unit, and a system management bus (SMBus(tm)) v1.1-compliant master/slave SMBus interface. The 8-bit, RISC microcontroller core has an integrated 8KB of user-programmable flash and a 12KB program ROM library, which provides battery-pack designers with complete flexibility in developing fuel-gauging and control algorithms. The MAX1789 is equipped with in-system debug (ISD) capability for efficient development and debugging. The MAX1789 includes a 12-bit data-acquisition unit to measure individual cell voltages, thermistors, current, and pack voltage. Internally adjustable overcurrent thresholds and delay timers provide a flexible solution. The integrating fuel-gauge module provides a typical input offset of less than 1 μ V and gain accuracy of better than 1% with no trimming required during pack manufacture. The MAX1789 has a wide +4V to +25V operating voltage range. The MAX1789 is available in a 28-pin TSSOP package. The MAX1789 evaluation kit is available to assist with development.

II. Manufacturing Information

A. Description/Function:	Advanced, Smart Battery-Pack Controller
B. Process:	S4
C. Number of Device Transistors:	372078
D. Fabrication Location:	California, Texas or Japan
E. Assembly Location:	Philippines, Thailand
F. Date of Initial Production:	January 24, 2009

III. Packaging Information

A. Package Type:	28-pin TSSOP
B. Lead Frame:	Copper
C. Lead Finish:	100% matte Tin
D. Die Attach:	Conductive
E. Bondwire:	Au (1 mil dia.)
F. Mold Material:	Epoxy with silica filler
G. Assembly Diagram:	#05-9000-3261
H. Flammability Rating:	Class UL94-V0
I. Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C	Level 1
J. Single Layer Theta Ja:	78°C/W
K. Single Layer Theta Jc:	12.5°C/W
L. Multi Layer Theta Ja:	71.6°C/W
M. Multi Layer Theta Jc:	13°C/W

IV. Die Information

A. Dimensions:	108 X 170 mils
B. Passivation:	Si ₃ N ₄ /SiO ₂ (Silicon nitride/ Silicon dioxide)
C. Interconnect:	Al with Ti/TiN Barrier
D. Backside Metallization:	None
E. Minimum Metal Width:	Metal1 = 0.5 / Metal2 = 0.6 / Metal3 = 0.6 microns (as drawn)
F. Minimum Metal Spacing:	Metal1 = 0.45 / Metal2 = 0.5 / Metal3 = 0.6 microns (as drawn)
G. Bondpad Dimensions:	5 mil. Sq.
H. Isolation Dielectric:	SiO ₂
I. Die Separation Method:	Wafer Saw

V. Quality Assurance Information

A. Quality Assurance Contacts:	Richard Aburano (Manager, Reliability Operations) Bryan Preeshl (Managing Director of QA)
B. Outgoing Inspection Level:	0.1% for all electrical parameters guaranteed by the Datasheet. 0.1% For all Visual Defects.
C. Observed Outgoing Defect Rate:	< 50 ppm
D. Sampling Plan:	Mil-Std-105D

VI. Reliability Evaluation

A. Accelerated Life Test

The results of the 135°C biased (static) life test are shown in Table 1. Using these results, the Failure Rate (λ) is calculated as follows:

$$\lambda = \frac{1}{\text{MTTF}} = \frac{1.83}{192 \times 4340 \times 48 \times 2} \quad (\text{Chi square value for MTTF upper limit})$$

(where 4340 = Temperature Acceleration factor assuming an activation energy of 0.8eV)

$$\lambda = 22.9 \times 10^{-9}$$

$$\lambda = 22.9 \text{ F.I.T. (60\% confidence level @ } 25^{\circ}\text{C)}$$

The following failure rate represents data collected from Maxim's reliability monitor program. Maxim performs quarterly life test monitors on its processes. This data is published in the Reliability Report found at <http://www.maxim-ic.com/qa/reliability/monitor>. Cumulative monitor data for the S4 Process results in a FIT Rate of 0.05 @ 25C and 0.83 @ 55C (0.8 eV, 60% UCL)

B. Moisture Resistance Tests

The industry standard 85°C/85%RH or HAST testing is monitored per device process once a quarter.

C. E.S.D. and Latch-Up Testing

The UC14 die type has been found to have all pins able to withstand a HBM transient pulse of +/- 2500V per JEDEC JESD22-A114. Latch-Up testing has shown that this device withstands a current of +/- 250mA and overvoltage per JEDEC JESD78.

Table 1
Reliability Evaluation Test Results

MAX1789EUI+

TEST ITEM	TEST CONDITION	FAILURE IDENTIFICATION	SAMPLE SIZE	NUMBER OF FAILURES
Static Life Test (Note 1)				
	Ta = 135°C Biased Time = 192 hrs.	DC Parameters & functionality	48	0
Moisture Testing (Note 2)				
HAST	Ta = 130°C RH = 85% Biased Time = 96hrs.	DC Parameters & functionality	77	0
Mechanical Stress (Note 2)				
Temperature Cycle	-65°C/150°C 1000 Cycles Method 1010	DC Parameters & functionality	77	0

Note 1: Life Test Data may represent plastic DIP qualification lots.

Note 2: Generic Package/Process data