





DIMENSIONS mm (inches)



PART NUMBER	8609	76	8	
PIN OUT				
rows a-b-c	3	24		
rows a-c	4	16		
NUMBER OF CONTACTS				
TERMINATION				
L = 2.70 ±0.25 (.106)				24
L = 4.65 ±0.25 (.183)				14
OPTIONS				
no option				7
with harpoons				H
PERFORMANCE CLASS				
DIN 41612 class 3				4
DIN 41612 class 2				5
DIN 41612 class 1				6
TERMINATION TYPE				
LEAD FREE				E1LF

PCB DRILLING



FCI

Copyright FCI.

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C-8609-0000A

rev	ecn no	dr	date
A	-	MJA	2012-08-09

www.fciconnect.com				surface	tolerance std	projection	mm
				ISO 1302	ISO 406 ISO 1101		
TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M JACOB	2012-06-27		ANGULAR	0.X	±0.1	size
Eng	M JACOB	2012-06-27		LINEAR	0.XX	±0.1	A3
Chr	M JACOB	2012-06-27	0.XX ±2		0.XXX	±0.1	ECN
Appr	BIJU K PAUL	2012-06-27	Product family	DIN 8609	Spec ref	-	Scale 1.5
FCI							
title STRAIGHT MALE - STYLE R/2				dwg no		Rev. A	
SOLDER TO BOARD				C-8609-2292			
catalog no				-		CUSTOMER sheet 1 of 1	