

SPECIFICATION FOR APPROVAL

規 格 書

Customer (客戶 名稱): _____

Customer P/N(客戶番號): _____

Our P/N (本廠番號): FS7040W0870-H28

Approval Date(日期): 2020.6.18

Environment Request(環 境 標 准):

☐ Non-RoHS (非 RoHS 標準)

☒ RoHS (RoHS 標準)

☐ REACH (REACH 標準)

☐ Others (其他)

CUSTOMER'S APPROVED SIGNATURE



泰州福聲電子科技有限公司

Taizhou Fusheng Electronic Technology Co.,Ltd.

Adds: No168 of FengHuang Road West,Hailing District ,Taizhou .

地址：江蘇省泰州市海陵區鳳凰西路98號

Tel: +86-523-86219066

Fax: +86-523- 81601108

[Http://www.tzfsdz.com](http://www.tzfsdz.com)




E-mail: sales@electronic-tech.cn

	DESINGER	CHECKED	APPROVED
SIGNATURE			
DATE			


Speaker Specification

Part No.	Customer No 顧客型號		Customer code 顧客編號	
	Our Part No 本廠編號	FS7040W0870-H28		Revision 版本 B
No.	Item 項目	Specification 規格	Testing Condition 測試條件	
1.	Rated Imp 共稱阻抗	8ohm±15%		
2.	Resonance Freq 最低共振周波數	350Hz±20%	Without Baffle	
3.	Output S.P.L. 出力音壓	84±3dB	At 0.1m/0.1w ,0.6,0.8,1.0,1.2KHz Average	
4.	Rated Power 定格入力	at 7.0W	at 7.48Vrms	
5.	Max Power 最大入力	at 8.0W	at 8.0Vrms	
6.	Frequency Range 實效頻寬	FO----20kHz		
7.	Operation 可靠性試驗	Must Be Normal at Rated Frequency Range	Program Source 7 W FO ----- 10kHz	
8.	Buzzes & Rattles 異常音試驗	Should not be audible buzz and rattle at Rated Frequency Range 無異常聲	Sine Wave Between (正弦波入力) at 7 . 4 8 Vrms / FO----10kHz	
9.	T H D 失真	≤5%		
10.	Magnet 磁鐵	Ferrite		
11.	Operating Temperature 動作溫度	-30℃ to +75℃		
12.	Storage Temperature 儲存溫度	-40℃ to +85℃		
13.	Weight 重量	92g±8%		


产品尺寸 Dimension picture:



产品图片Picture:



Frequency Response



Remark

NO	零件Component	材质Material
1	压边 Gasket	纸 Paper
2	盆架 Frame	冷轧钢板SPCC
3	弹波 Damper	布 Cloth
4	华司Washer	冷轧钢板SPCC
5	磁铁 Magnet	铁氧铁 Ferrite
6	T铁 T-Yoke	冷轧钢板SPCC
7	音圈Voice Coil	胶管 KSV +Cu
8	鼓纸 Cone	泡边纸盆Foam+Paper
9	帽子 Dust cap	纸Paper
10	接线板 Terminals	纸+铁 Paper+Steel

包装Packing picture:



- 1.Each clapboard 30pcs,
Each carton 4 clapboards,
150 pcs/carton
N.W: 13.8 KG, G.W:15.8 KG
- 2.Corrugated paper: 460*330mm 1 pcs
- 3.Carton size: 475*345*225mm 1 pcs

