

A	Dept	1	2	3	4	5	6	7	8	A
	Qty	晨翔2.0mm TJC8 TYPE 黑色1*10pin胶芯				REV.	DESCRIPTION	DRAWN	CHECKED	
	DC	1					A	NEW RELEASE	WPY 11/14/24'	
	ED	1								
	IE	1	晨翔料号: I-DS1071-01-SCB01x10							
B	ISO	1								B
	PD	1								
	R&D	1								
	SD	1								
	QA	1								
C	QC	1								C
	QE	1								
D										D
E										E
F										F
G										G
H										H

晨翔2.0mm TJC8 TYPE 黑色1*10pin胶芯

晨翔料号: I-DS1071-01-SCB01x10

备注:

- 电性说明:
 - 耐压: 500伏交流电一分钟
 - 绝缘阻抗: 500兆欧最小
 - 额定电流: 2安
- 环境特性:
 - 工作温度: -25~+85° C
- 材料:
 - 胶芯: PA66, 黑色
- 产品符合欧盟RoHS环保要求

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	
X.	±0.60	X.	±5°	UNITS	mm	2.0mm TJC8 TYPE 黑色1*10pin胶芯	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1071-01 SERIES
.XX	±0.25	.XX	±2°	晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			
DRAWING TYPE		CUSTOMER					
SCALE	1:1	SHEET	1 OF 1				
DRAWING NO.		C-DS1071-01-XXXXX-A					