






带@符号为重点尺寸,



PART NO	Dim. A	Dim. B
FC-6P	5.08	12.32
FC-8P	7.62	14.86
FC-10P	10.16	17.40
FC-12P	12.7	19.94
FC-14P	15.24	22.48
FC-16P	17.78	25.02
FC-18P	20.32	27.56
FC-20P	22.86	30.10
FC-24P	27.94	35.18
FC-26P	30.48	37.72
FC-28P	33.02	40.26
FC-30P	35.56	42.80
FC-34P	40.64	47.88
FC-40P	48.26	55.5
FC-50P	60.96	68.20
FC-60P	73.66	80.90
FC-64P	78.74	85.98

MATERIAL&FINISH

Insulator: PBT Glass Fiber(UL94V-0)

Contact : Brass

Contact : Gold-Plated Over Nickel.

SPECIFICATIONS

Current Rating :1A AC,DC

Voltage Rating : 250V AC,DC

Temperature Range:-40° C To+105° C

Contact Resistance:20mΩ Min

Insulation Resistance:1000MΩ Min

Withstanding Voltage:500V AC/Min

UNLESS OTHERWISE SPECIFIED TOLERANCE : X. ±0.20 ANGLES : ±2° X.X ±0.15 X.XX ±0.10 DO NOT SCALE DRAWING		浙江博穆精密电子有限公司		
DRAWN BY	毛平	TITLE 2.54/IDC塑胶产品图		001
CHECKED BY		SIZE A	UNIT MM	PART NO. CSD-WI-EG-OA-001
APPROVED BY		SCALE	THIRD ANGLE PROJECTION	
DWG NO.		ITEM NO.		DATE 09/07/2006