



	1	2	3	4	5	6	7	8					
A	Dept	晨翔2.54mm TJC8 TYPE 黑色1*3pin胶芯				REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A		
	Qty					A	NEW RELEASE	WPY 11/09/24'					
	DC	1											
	ED	1											
	IE	1	晨翔料号: I-DS1071-SCB01x3										
	ISO	1											
	PD	1											
	R&D	1											
B	SD	1											
	QA	1											
	QC	1											
	QE	1											
C						备注: 1. 电性说明: 1.1 耐压: 500伏交流电一分钟 1.2 绝缘阻抗: 1000兆欧最小 1.3 额定电流: 3安 2. 环境特性: 2.1 工作温度: -25~+85° C 3. 材料: 3.1 胶芯: PA66, 黑色							
D													
E													
F													
G													
H													
GENERAL TOLERANCE						ANGLE TOLERANCE		PROJECTION		TITLE			
X. ±0.60						X. ±5°				2.54mm TJC8 TYPE 黑色1*3pin胶芯			
.X ±0.38						.X ±3°		UNITS mm					
.XX ±0.25						.XX ±2°		SHEET SIZE A4		SERIES DS1071 SERIES			
DRAWING TYPE						CUSTOMER						 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD	
SCALE						1:1		SHEET		1 OF 1			
DRAWING NO.						C-DS1071-XXXXX-A							