






1. Electrical Characteristics

- 1.1 Impedance: 50 Ohm
- 1.2 Working Frequency: DC - 6 GHz
- 1.3 V.S.W.R. : ≤ 2.0
- 1.4 Working Voltage: 335V / max
- 1.5 Withstand Voltage: 750V RMS
- 1.6 Insulation Resistance: 5000 Mohm
- 1.7 Contact Resistance: Center Contact: 5mohm
- 1.8 Outer Contact: ≤ 2.5 mohm

2. Environmental

- 2.1 Working Temperature Range: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$



8	PIN针 OD1.50*9.70	黄铜 镀金	SMA015097G-1948	1
7	本体 $\phi 9.50 \times 8.60 \times 2.40$	锌合金 镀镍	SMA095086N-1254	1
6	绝缘体 OD4.50*9.70	PTFE 白色	SMA045097I-1610	1
5	内置本体 OD7.00*9.70	黄铜 镀镍	SMA070097N-0901	1
4	华司 OD7.50*0.70	黄铜 镀镍	SMA075007N-1024	1
3	防水圈 OD7.00*1.00	硅胶 红色	ORI070010X-0542	1
2	外壳 $\phi 12.9 \times 8.90$	POM 黑色	SMA129089B-2235	1
1	螺牙本体 $\phi 8.50 \times 8.30$	黄铜 镀镍	SMA085083N-1226	1
部件序号	部件品名/规格	材料	零件编号	用量

Rev.	Date.	变更单号	变更者	Description. 内容
ECN No.				

Tolerance 未标注公差:		HJ-Tech 东莞市皇捷通讯科技有限公司	
. X ± 0.2		DONGGUAN HUANGJIE COMMUNICATION TECHNOLOGY CO., LTD.	
. XX ± 0.10		Part Name. 品名/规格	RP SMA PLUG S/T FOR ANTENNA
. XXX ± 0.05		C/U Part No. 客户料号	
未标注角度公差 $\pm 1^{\circ}$		PartNo. 料号	2LC15PF604
		Draw . 繪圖	Check 校對
		版本 次	A 0
		單位	mm
		瑞芬	2019. 10. 22