






General tolerances(mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

0.1/10

±2°



Product model	PIN	A	B
XDCB-2A381G-4-3G61	2	8.41	3.81
XDCB-3A381G-4-3G61	3	12.22	7.62
XDCB-4A381G-4-3G61	4	16.03	11.43
XDCB-5A381G-4-3G61	5	19.84	15.24
XDCB-6A381G-4-3G61	6	23.65	19.05
XDCB-7A381G-4-3G61	7	27.46	22.86
.....			
XDCB-24A381G-4-3G61	24	3.81xN+0.79	3.81x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/8	/	300/8
IEC Standard			
Overvoltage Category/Pollution Degree	II/2		
Rated Voltage(V)/Current(A)	250/7		
Rate Impulse Voltage(KV)	2.5		
Torque Tightening(N·m/Lb.in)	M2, 0.2/1.77		
Wire Range(rigid and flexible)(mm ² /AWG)	0.5~1.5/28~16		
Pitch(mm)/Poles	3.81/N=02~24P		
Stripping length(mm)	6~7		
Operating temperature(°C)	-40°C~+105°C		
Conform to RoHS	Yes		

ITEM	NAME OF PART	MATERIAL	NOTES
5	Clamp	Copper Alloy	Sn Plated
4	Screw	Steel	M2/Zn Plated
3	Cage	Copper Alloy	M2/Ni Plated
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: Socket-type terminal			
.X±0.35	X.*±1°	APR.	Alex	DWG NO. XDCB-NA381G-4-3G61	
.XX±0.15	.X.*±0.5°	CHK.	Jack	PROJ.	
.XXX±0.10	.XX.*±0.5°	DRA.	Can	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 2/1	REV. A		