






REV.	REVISION DESCRIPTION	DATE	

- NOTES:
- 1、Rated voltage: 150V AC.DC
 - 2、Rated current: 10A AC.DC
 - 3、Contact resistance: $\leq 20\text{ m}\Omega$
 - 4、Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5、Withstand voltage : 1500V AC/minute
 - 6、Ambient temperature: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$
 - 7.Materials: Nylon UL94V-0(2)
 - 8.Green Material RoHS Compliant



PCB LAYOUT



Circuits	PRODUCT NAME	Dimension mm	
		A	B
2X1	XL-2A	—	8.15
2X2	XL-4A	5.00	13.15
2X3	XL-6A	10.00	18.15
2X4	XL-8A	15.00	23.15
2X5	XL-10A	20.00	28.15
2X6	XL-12A	25.00	33.15
2X7	XL-14A	30.00	38.15
2X8	XL-16A	35.00	43.15
2X9	XL-18A	40.00	48.15
2X10	XL-20A	45.00	53.15
—	—	—	—

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: XL-A		TITLE: 5.0 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long		DATE:19/08/01	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD:Wu Hui		DATE:19/08/01	
FINISH: _____		APPD:Ren An De		SCALE: N/A	
DRAWING NO:		DATE:19/08/01		UNITS: mm	PAGE: 1/1
				REV.: A	




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:


- 1、Rated voltage: 150V AC.DC
- 2、Rated current: 10A AC.DC
- 3、Contact resistance: $\leq 20\text{ m}\Omega$
- 4、Insulation resistance: $\geq 1000\text{ M}\Omega$
- 5、Withstand voltage : 1500V AC/minute
- 6、Ambient temperature: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$
- 7.Materials: Nylon UL94V-0(2)
- 8.Green Material RoHS Compliant



2PIN




4PIN



Circuits	PRODUCT NAME	Dimension mm	
		A	B
2X1	XL-2Y	—	6.20
2X2	XL-4Y	5.00	11.20
2X3	XL-6Y	10.00	16.20
2X4	XL-8Y	15.00	21.20
2X5	XL-10Y	20.00	26.20
2X6	XL-12Y	25.00	31.20
2X7	XL-14Y	30.00	36.20
2X8	XL-16Y	35.00	41.20
2X9	XL-18Y	40.00	46.20
2X10	XL-20Y	45.00	51.20
—	—	—	—

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: XL-Y		TITLE: 5.00 mm Pitch Housing	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:19/08/01	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL50005-Y Series Housing.

Material : Phosphor Bronze .

Finish: Tin plated.

Thickness: 0.25 mm.

TYPE	Dimension mm				适用线规 AWG#
	A1	B1	A2	B2	
XL-T-G	4.5	4.0	3.1	2.6	20-16
XL-T-D	3.3	3.3	2.2	1.9	26-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: XL-T	TITLE: 5.0 mm Pitch Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:20/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:20/08/01	PART NO:
FINISH:		CHKD: Wu Hui	DATE:20/08/01
DRAWING NO:	APPD:Ren An De	DATE:20/08/01	SCALE: N/A
			PAGE: 1/1
			UNITS: mm
			REV.: B