

1 2 3 4 5

晨翔2.54mm TJC8 TYPE 母端子 全锡

晨翔料号: T-DS1071-SC600

Technical drawing of a 2.54mm pitch TJC8 type female terminal. The drawing includes a top view, a side view, and a detail view of the terminal body.

Top View Dimensions:

- Width: 6.00
- Height: 14.70
- Pin Diameter: $\phi 1.50$

Side View Dimensions:

- Terminal Thickness: T=0.20
- Terminal Height: 1.8
- Terminal Body Height: 11.5

Detail View Dimensions:

- Terminal Body Height: 2.7
- Terminal Body Width: 1.6
- Terminal Body Thickness: 2.6


电线规格	
截面积 (mm ²)	AWG#
0.09~0.3	28~22

GENERAL TOLERANCE		ANGLE
X.	±0.60	X.
.X	±0.38	.X
.XX	±0.25	.XX

DRAWING TYPE	CUSTOMER	
SCALE	1:1	SHEET
DRAWING NO.	C-DS1071	

备注:

1. 电性说明:
 - 1.1 耐压: 500伏交流电一分钟
 - 1.2 绝缘阻抗: 1000兆欧最小
 - 1.3 额定电流: 3安
2. 环境特性:
 - 2.1 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
3. 材料:
 - 3.1 端子: PA66, 黑色



GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°
DRAWING TYPE		CUSTOMER	
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1071-XXXXX-A		

PROJECTION		TITLE	2.54mm TJC8 TYPE 母端子 全锡
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1071 SERIES
 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			