










1.FIGURE AND DIMENSIONS(视图及尺寸)



1. Mating (插拔次数)		5000次
2. Working Temperature (温度)		-40~+105 °C
3. IP Rating (防护级别)		IP 65
4. Contact plating material (触点电镀材料)		-
5. Contact resistance (触点电阻)		10M Ω
6. Working Voltage (工作电压)		125V
7. Rated Current (额定电流)		见参数表
8. shell material (壳体材质)		锌合金
9. Pin Material (插针材料)		黄铜

孔位排列						
(芯数)	2P (2)	3P (3)	4P (4)	5P (5)	6P (6)	7P (7)
额定电流	额定电流: 5A	额定电流: 5A	额定电流: 5A	额定电流: 3A	额定电流: 3A	额定电流: 3A

版本	TITLE					DRAWING NO.		REV.
REVA4						EG. GX12. P04. CAL		A0
REVA3								
REVA2								
REVA1								
DRAW								
CHECK						USE		 
APPR'D								
PART NO.						UNIT	mm	
						SCALE	Free	
						SHEET	10F N	
						XKB INDUSTRIAL PRECISION CO., LIMITED		