









1.FIGURE AND DIMENSIONS(视图及尺寸)



1. Mating (插拔次数)		5000次
2. Working Temperature (温度)		-40~+105 °C
3. IP Rating (防护级别)		IP 65
4. Contact plating material (触点电镀材料)		-
5. Contact resistance (触点电阻)		10M Ω
6. Working Voltage (工作电压)		125V
7. Rated Current (额定电流)		见参数表
8. shell material (壳体材质)		锌合金
9. Pin Material (插针材料)		黄铜

孔位排列						
(芯数)	2P (2)	3P (3)	4P (4)	5P (5)	6P (6)	7P (7)
额定电流	额定电流: 5A	额定电流: 5A	额定电流: 5A	额定电流: 3A	额定电流: 3A	额定电流: 3A

版本				TITLE	DRAWING NO.	REV.
REVA4					EG. GX12. P07. CAL	A0
REVA3						
REVA2						
REVA1						
DRAW		DATE		PART NO.	UNIT	mm
					SCALE	Free
					SHEET	10F N
CHECK		DATE		USE	 	
APPR'D		DATE				
				XKB INDUSTRIAL PRECISION CO.,LIMITED		