








P.C.B LAYOUT
TOLERANCE:±0.05



Ordering Information:

D1272WV-S-F-XP - ** - *** - ***
1 2 3 4

1.Part NO.

2.Size (H):

(Blank): 6.40mm

L: 4.10mm

3.Color:

(Blank): Black

IV: Ivory

4.Finish:

(Blank): Tin over Nickel

G: Gold over Nickel(Au:1µin[0.03µm] Min)

G3: Gold over Nickel(Au:3µin[0.08µm] Min,Mating Area)

SPECIFICATIONS:

Current Rating: 1.2A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage:500V AC/minute

Terminal Material: Copper Alloy

Housing Material: LCP,UL94V-0

Ordering Information & Dimensions

Part NO.	Dimensions(mm)	
	A	B
D1272WV-S-F-4P	3.81	8.86
D1272WV-S-F-6P	6.35	11.40
D1272WV-S-F-8P	8.89	13.94
D1272WV-S-F-10P	11.43	16.48
D1272WV-S-F-12P	13.97	19.02
D1272WV-S-F-14P	16.51	21.56
D1272WV-S-F-16P	19.05	24.10
D1272WV-S-F-18P	21.59	26.64
D1272WV-S-F-20P	24.13	29.18
D1272WV-S-F-22P	26.67	31.72
D1272WV-S-F-24P	29.21	34.26
D1272WV-S-F-26P	31.75	36.80

CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE	
mm	1:1	1 of 1		
DRWN	CHKD	APPR	1.27mm IDC 180° WAFER - SMD TYPE	
Dengchun Yi	Diankui Wan	Jack Yin		
General Tolerances			THIRD ANGLE PROJECTION	DRAWING NO. D1272WV-S-F-XP
A1	CHANGE THE DRAWING	2020.07.16		
A0	NEW RELEASE	2017.01.10		REV A1
REV	DESCRIPTION	DATE		