







NOTES:

- METAL SHELLS: STEEL; TIN PLATED
- INSULATORS: PBT GF, UL 94 V-0; GREEN
- CONTACTS: COPPER ALLOY
- PLATING: MIN. 30µ" HARD GOLD OVER MIN. 50µ" NICKEL



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH

rev.	description	date	name

tolerance	scale	material	title
	2:1 (5:1)	SEE NOTES	

D-SUB COMBINATION MALE 5W/P SOLDER CUP		dwg no: 13K11T8A		CAD/ REL.14 DIN-A 3		sh: 1/1	



product no: 3005W/PCMH99A10X

used for: D-SUB COMBINATION