




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AP-145-1M	1	SHELL ASS'Y	303 SS & NEOPRENE
2	AP-146-6	1	INSERT ASS'Y	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER

NOTES:
1) UNLESS OTHERWISE SPECIFIED, THIS CONNECTOR MEETS ALL
GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116
2) MATES WITH U-283/U PANEL MOUNT CONNECTOR & U-328/U
INLINE CONNECTOR



B

AP-146MNB-CP



SECTION Y-Y
SCALE 3.000

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

B	DEL:..35(C-2), ADD: 1.31	235	3/21 2017	HR
A	NEW RELEASE		10/6 2016	HR
LET.	REVISION	CN #	DATE	CHK.

DWN.BY HR	DATE 10/6/16	MATERIAL	
CHECKED BY	DATE	FINISH	
APPR.BY	DATE	WEIGHT —	SCALE = 1.00 :1
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES &/OR [mm] TOLERANCES: DECIMAL: .XX[X.X] .XXX[X.XX] ± .01[0.3] ± .005[0.13] FRACTION: X/X 1/64 ANGLES: X ± .5°		TITLE AUDIO PLUG	
		DO NOT SCALE DWG. SHEET 1 OF 1	
		SIZE B	DWG. NO. AP-146MNB-CP