



Pushing Performance
Since 1945

16 B Hood TE LC 4 Pegs PG 21 Black



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 716 1420
Specification	16 B Hood TE LC 4 Pegs PG 21 Black
HARTING eCatalogue	https://b2b.harting.com/09307161420

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® B
Type of hood/housing	Hood
Description of hood/housing	Black
Type	Low construction

Version

Size	16 B
Version	Top entry
Cable entry	1x Pg 21
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP66 IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	140.2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048744
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors