





DESCRIPTION: M12 FEMALE - PANEL MOUNT (REAR) - SOLDER CUP - 8 POS.



PANEL CUTOUT



NUT



## NOTE:

### MATERIAL

|           |                    |
|-----------|--------------------|
| HOUSING:  | PBT UL94V-0, BLACK |
| CONTACT:  | BRASS              |
| SHELL:    | BRASS              |
| NUT:      | BRASS              |
| O-RING A: | EPDM, BLACK        |
| O-RING B: | EPDM, BLACK        |

### FINISH

|              |               |
|--------------|---------------|
| CONTACT:     | GOLD PLATED   |
| UNDER PLATE: | NICKEL        |
| SHELL:       | NICKEL PLATED |
| NUT:         | NICKEL PLATED |

### ELECTRICAL

|                        |                |
|------------------------|----------------|
| RATED CURRENT:         | 2A             |
| RATED VOLTAGE:         | 30V            |
| INSULATION RESISTANCE: | 100 MOhms MIN. |
| CONTACT RESISTANCE:    | 10 mOhms MAX.  |
| WATER PROOF:           | IP67           |


### ENVIRONMENT

|                        |                |
|------------------------|----------------|
| OPERATION TEMPERATURE: | -40°C TO +85°C |
| MAX WIRE AWG:          | 24             |

859-008-203R00Y

3 = BRASS/NICKEL SHELL & NUT  
S = STAINLESS STEEL SHELL & NUT

1 = GOLD FLASH  
4 = 10u" GOLD



RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-07-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

859-008-203R00Y