

ZZE ZP2.5/8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The strain relief protects the contact against mechanical stress and protects the connector against inadvertent release from the contact point.

General ordering data

Version	Z-series, Strain relief, yellow, 30.1 mm
Order No.	1866230000
Type	ZZE ZP2.5/8
GTIN (EAN)	4032248480838
Qty.	25 pc(s).

ZZE ZP2.5/8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5.62 mm	Depth (inches)	0.221 inch
Height	75.9 mm	Height (inches)	2.988 inch
Width	30.1 mm	Width (inches)	1.185 inch
Net weight	3.6 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	100		

Material data

Material	PA 66 GF 30	Colour	yellow
UL 94 flammability rating	HB		

System specifications

Version	Strain relief
---------	---------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	