

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PREPONT, ILLINOIS
FED. MFR. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING

JS-49

JS-49

M

DRAWING
NUMBER

8

X

ISSUE

3

(M) SKETCH 16058

REPLACES ISSUE 1

RELEASE NO. S.R. 6568

CHECK

REVISIONS

A CO12901

MBF

18 MAY 59

B CO17304

MBF

4 DEC 63

CNT

25 MAY 59

6CH

28 MAY 59

CHECK

24 MAY 57



K. A. F.

DRAWN

FO-80378

(B) A495 MAX
FREE POSITION

(A) 41
OPERATING POSITION



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISMI BASIC SWITCH INSTALLED

OPERATING FORCE-----18 OZ MAX
RELEASE FORCE-----2 OZ MIN
PRETRAVEL-----.125 MAX
DIFFERENTIAL TRAVEL-----.015 MAX
OVERTRAVEL-----.015 MIN

(A)

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ± 2°

WEIGHT