


REVISION		
REV	DESCRIPTION	DATE
G	REVISED PER ECO-18-008206	29MAY2018



Notes:

1. Application: Electroless Nickel MTC SH2 Plug Shells
2. For Use With MIL-C 39029/58-360, Size 22 Contacts
3. End Cap: Glass Filled Nylon, Flame Retardant, Black
4. Main Body: Aluminum, Electroless Nickel Plated
5. Screws: 4-40 Phillips Head, Stainless Steel 302, Passivated, Captive, Self-Locking. Alternative material A-286
6. Electrical Contacts: Brass / Beryllium Copper, Gold Plated
7. Markings: High Contrast Ink
8. Bus Bar, Beryllium Copper, Electroless Nickel Plated
9. Meets Raychem Specification C-6114 Requirements
10. Contact Cavity Bore Dia, Plated: .0685/.0690 (REF)

© 2004 TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

			SPECIFICATION CONTROL DRAWING				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES. METRIC DIMENSIONS ARE IN BRACKETS. DECIMAL TOLERANCES .XXX ± 0.005 [0.13 mm] .XX ± 0.010 [0.25 mm] .X ± 0.020 [0.50 mm] ANGLE TOLERANCE .X ± 0.5 DEG. WEIGHT (NOM) LBS. 0.0216 [9.8 gm]	DRAWN	DATE	tyco Electronics		TYCO ELECTRONICS 300 CONSTITUTION DRIVE MENLO PARK, CA 94025	Raychem	
	T RATZLAFF	26MAR2004					
	MATERIAL	SEE NOTES		TITLE 2-INCH MTC GROUNDING BLOCK WITH FINGERS			
	FINISH	SEE NOTES					
CAD FILE C041090.DWG	THIRD ANGLE PROJECTION				SIZE	CAGE CODE	DWG. NO.
					A	06090	CHA-0308
DO NOT SCALE THIS DRAWING					SHEET 1 OF 1		