

Technical Characteristics

Part Number

Han® 1A Kit

Hood	Top Entry
Housing	Snap-In Angled Bulkhead
Material	Polyamide Plastic
Protection Degree	IP65
Temp Rating	-30 to +90C
Cable Gland	Plastic
Cable Diameter	5.7 – 10mm
Insert	3+GND
Screw Terminals	18-14AWG
Wire Strip Length	7.5mm
Mating Cycles	>100
Flammability	V-0

Electrical Characteristics



Rated Current	10amps
Rated Voltage acc. UL	250V
Rated Impulse Voltage	6kV

73 10 100 0018



Drawings and Assembly Information

Dimensions in mm



Tooling and Torque Values

Type	Tool	Torque (Nm)
Terminal Screws (M3)	Slotted 0.4 x 2.5	0.25
Mounting Screws (M3 recommended)	-	0.3
Recommended Punch Die	09990000973	-

Kit Contents

Male Insert	09 10 003 2601
Female insert	09 10 003 2701
Housing	09 10 000 0800
Hood & Gland	09 10 000 0400

For further information, please reach out to
techsupportUS@HARTING.com