

Coaxial Cable Connector 11_QLA-01-3-2/122_N

Description

Straight cable plug

Interface standards

NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

| | |
|--------------------------|---------|
| Impedance | 50 Ω |
| Interface frequency max. | 1.4 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0051 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -55 °C to 150 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Nickel Plating |
| Body | Brass | Nickel Plating |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Catalogue drawing | DOU-00006540 |
| Assembly instruction | DOC-0000180108 |

Ordering Information

| | |
|----------------|----------------------|
| Single package | 11_QLA-01-3-2/122_NE |
|----------------|----------------------|

Additional Information

| | |
|-----------------|-----------------------|
| Suitable cables | RG_223_/U, RG_142_B/U |
|-----------------|-----------------------|