


LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REV PER ECO-06-027267	05DEC2006	RG	DO




1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING THE INTERCHANGEABILITY REQUIRE PRIOR TYCO APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.
2. MATERIAL:
INSULATOR: THERMOPLASTIC, GLASS REINFORCED, UL 94V-0
FLAMMABILITY RATED, COLOR: BLACK
PIN CONTACT: TELLURIUM COPPER ALLOY CI4500
RETENTION CLIP: BERYLLIUM COPPER
3. FINISH:
CONTACTS: SILVER PLATED .000200 MIN THK. OVER NICKEL .000040 MIN. THK. GOLD PLATE .000030 MIN. THK. OVER NICKEL .000040 MIN. THK.
4. ITEMS PROVIDED TO THIS SPECIFICATION TO BE PERMANENTLY IDENTIFIED PER THE FOLLOWING IDENTIFIER:
- TYCO PART NUMBER: XXXXXX-X
- DATE CODE (e.g. 0216): YEAR WEEK
5. CRIMP CONTACTS (ITEM D) SHALL BE PACKAGED SEPARATELY AND PLACED IN THE BOX WITH THE CONN. ASSEMBLY.

5	D	3	6648318-1	CONTACT, SOCKET, #12, CRIMP, STD
	C	24	1648382-1	CONTACT, SOCKET, #20, PCB TAIL, STD
	B	4	6648417-1	CONTACT, SOCKET, #0, 1/4-20 EXT. THD.
	A	1	1648578-1	CONNECTOR, SOCKET, NO GUIDE PINS
	ITEM	- 1	PART NUMBER	DESCRIPTION


ELCON

DRAWER

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



SUGGESTED PCB LAYOUT



SUGGESTED PANEL CUTOUT
VIEWED FROM CONNECTOR MOUNTING SIDE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN R. GRZYBOWSKI 01FEB2006	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK P. DAMATO 01FEB2006	NAME DOUBLE DRAWER CONNECTOR SOCKET			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER 01FEB2006	-			
		PRODUCT SPEC -	-			
		APPLICATION SPEC -	-			
MATERIAL -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-6766346	RESTRICTED TO -
FINISH -		CUSTOMER DRAWING	SCALE 2:1		SHEET 2 OF 2	REV D