

Disassembly tool for LUMOTAST 25, RAFIX 16

5.05.800.042/0000



General information

Fitting for LUMOTAST 25, RAFIX 16

Other specifications

Shock resistance acc. to IEC 60068-2-27 amplitude < 50g, 11ms, half sinusoidal

Ambient temp. operating min. -25 °C

Ambient temp. operating max. with lamp /LED +55 °C

Storage temperature min. -40 °C

Storage temperature max. +85 °C

Environmental resistance acc. to IEC 60068-2-14, -30, -33 and -78

Hot wire ignition acc. to IEC 60695-2-1 yes

Resistance to vibrations acc. to IEC 60068-2-6 10 g at 20 ... 500 Hz

ROHS compliant yes

REACH compliant yes

