

Between Series Adaptor 34_BNC-QLA-01-1/1--_U

Description

Bulkhead adaptor jack/jack
BNC jack (female) / QLA-01 jack (female)

Interface standards
Series BNC - IEC 61169-8_MIL-STD-348A/301_CEEC 22120
Series QLA-01 - NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	other Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Number of matings	500
Weight	0.0092 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014159
Mounting hole	DOU-00008762

Ordering Information

Single package	34_BNC-QLA-01-1/1--_UE
----------------	------------------------