




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/18	



SD-PNLXX-FFTAL-S00-000



SPECIFICATIONS:

Material:
Housing: Nylon 46, rated UL 94V-0, Color: Black
Contacts: Phosphor Bronze, 5u" min. Gold
Shell A: Zinc Alloy, Nickel plated
Shell B: Brass, Nickel plated
O-ring A: NBR, Color: Black
Screw: Alloy Steel, Nickel plated
Clamp: Brass
SR: TPR
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	$\pm .10$	$\phi .X$	$\pm .10$
.XX	$\pm .020$	$\phi .XX$	$\pm .015$
.XXX	$\pm .015$	$\phi .XXX$	$\pm .010$

APPROVALS		DATE
DRAWN	HR	11/23/18
CHECKED	AC	11/23/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WATERPROOF CONNECTOR, FEMALE M8 DIN,
ASSEMBLY, SCREW TYPE, SOLDER

SIZE X	PART NO. SD-PNLXX-FFTAL-S00-000	REV. -
REF: S00200T	SCALE: NTS	SHEET 1 OF 1