


PA0210C *Proto Advantage*

Datasheet revision 1.0


www.Proto-Advantage.com

TSOP-54 (II) to DIP-54 SMT Adapter (0.8 mm pitch, 10.16 mm body) *Compact Series*




REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		9.20				
B		3.00				
C		0.50				
D		0.30				
E		0.80				
F					0.600	
G					0.100	
H		0.46				
X					0.700	
Y					2.700	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)