

HUBER+SUHNER® DATA SHEET

Within Series Adaptor: 32_MMBX-50-0-9/111_N

Rev.: E



Description

Adaptor plug/plug
MMBX plug (male) / MMBX plug (male)
Slide - snap interface
Interface standard
Series MMBX - SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	12.4 GHz		
Frequency range	DC to 2.5 GHz	2.5 to 6 GHz	6 to 12.4 GHz
Return loss	≥ 26 dB	≥ 21 dB	≥ 12 dB

Mechanical Data

Number of matings	100
Weight	0.0003 kg

Environmental Data

Operating Temperature	-55 °C to 155 °C
2002/95/EC (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Interface - MMBX plug (male)		
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	
Interface - MMBX plug (male)		
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00063227

Ordering Information

Bulk 100 pcs package 32_MMBX-50-0-9/111_NH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions