





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190348	2019/03/06	Vicky	Change Note




With Liquid Glue



ACD-XXPMFS-LC7001
07: 7Pin
:
09: 9Pin



Pin Assignments Front View



- Note:
- * Ⓞ Important Dimension To Check.
 - * Waterproof Rate: IP67, Unmated.
 - * Housing: Thermoplastic, Black.
 - * Pin: Copper Alloy, Gold Plated.
 - * Nut: Thermoplastic, Black.
 - * Gasket: Rubber, Gray.
 - * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.8mm
 - * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm
 - * Gasket and Nut are packed separately
in PE bags. (Gasket/Nut不組裝, 散裝出貨)

UNIT: mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
.X ±0.25		.XX ±0.1		MIDDLE		ACD-XXPMFS-LC7001		Vicky		2019-03-06	
.XXX ±0.05		ANGLES ±1°		PANEL LOCK M CONN F PIN		CUSTOMER		Rita		2019-03-06	
SCALE 3:2		SIZE A4		SHEET 1 OF 1		ALTW		APPROVED BY		Max	
REV. B		WC-REV. A.2		QC: Inspection item						2019-03-06	

Amphenol LTW
安費諾亮泰企業股份有限公司