

Item number: S22L0C-P07PPL0-920S




(Example: image representation of the design)

ODU MINI-SNAP® connector
7-pin
connector - Protection class IP 50 with clamping nut for kink protection*
*Please order protective grommets separately
Housing: matt chrome-plated

Remember the product

Download PDF

Dimensions 		Number of poles: 7 poles 		contact insert 7-pin pin (single contacts) Crimp clip contact		Coding 0 ° 
Insulation material:		PEEK				
Contact diameter:		0				
Cable diameter:		from 8 mm to 8 mm				
Max. Connection cross section:		AWG 18/20 / 0.50 / 1.00				
		mm ²				
Connection		diameter	:	0 mm		
Technical specifications						
Continuity resistance		:	kA μΩ			
Insulation resistance:		10 ^ 16 Ω				
Air and creepage distance:		0 mm	according to IEC 60664-1: 2007 (VDE 0110-1: 2008)			
Current load Single contact:		0 A				
Current load compl. Application:		0 A	VDE 0298-4: 2013			
Test		voltage:	0 kV	SAE AS 13441: 2004 method 3001.1		
Rated voltage:		0 kV	SAE AS 13441: 2004 method 3001.1			

All dimensions in mm. All illustrations are illustrations. Subject to change.

General information about ODU MINI-SNAP Application
temperature: -40 ° C to + 120 ° C