










WIRING DIAGRAM



10	8	CONTACT M12 MALE	BRASS	SELECTIVE Au OVER Ni
9	1	INSERT MALE 8P AC BLACK	PA	---
8	-	POTTING MATERIAL 2-CMPT	PUR-BASE	---
7	1	LOCKNUT SW19 M16x1.5	BRASS	NICKEL
6	1	ORING Ø16mm BLACK	EPDM	---
5	-	WIRE 0.22mm²	PVC	---
4	1	ORING Ø7.1mm RED	FPM	---
3	1	INSERT FEMALE 8P AC BLACK	PUR	---
2	1	SHELL U12/M16/U12	BRASS	NICKEL
1	8	CONTACT M12 FEMALE	BRASS	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

NOTES:
CONTACT CURRENT RATING: 2A
VOLTAGE RATING: 30V
TEMPERATURE: -25°C / +85°C
INTERNATIONAL PROTECTION: SIDE 1 - IP 67/68/69K
SIDE 2 - IP65



QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
 = 0	EC NO: 110653 DRWN: JMARSZALEK CHK'D: RSILLER APPR: RSILLER	2016/11/16 2016/11/22	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE								
 = 0				MM		3:1								
 = 0				DRWN BY		DATE								
 = 0				ANGULAR TOL ± 1.0 °		JMARSZALEK		2016/08/11		REC U12 U12 8P AC FE MA M16 BULKHEAD				
 = 0				4 PLACES ±		CHK'D BY		DATE						
 = 0				3 PLACES ±		APPR BY		DATE						
 = 0				2 PLACES ± 0.05		RSILLER		2016/08/29		PRODUCT CUSTOMER DRAWING				
 = 0				1 PLACE ± 0.3		DRAWING SIZE		THIRD ANGLE PROJECTION						
				0 PLACES ± 0.5		A3								
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
A1		REV	SERIES								MATERIAL NUMBER		CUSTOMER	
			120084								1200848169		GENERAL MARKET	
			DOCUMENT NUMBER				DOC TYPE		DOC PART		SHEET NUMBER			
			1200848169				PSD		000		1 OF 1			