




- NOTES:
1. PARTS TO BE BULK PACKED.
2. ALL DIMENSIONS ARE REFERENCE ONLY.
DIMENSIONS IN BRACKETS [] ARE METRIC.




ASSEMBLED VIEW SHOWN
WITH STANDARD COUPLING RING











ASSEMBLED VIEW SHOWN
WITH WINGED COUPLING RING




FACE VIEW
W3280-12PG-5XX(W)




FACE VIEW
W3280-10PG-5XX(W)




WIRE VIEW



FACE VIEW
W3280-11PG-5XX(W)




ASSEMBLED VIEW SHOWN
WITH STANDARD
COUPLING RING



ASSEMBLED VIEW SHOWN
WITH WINGED
COUPLING RING

KIT PART NO.	GROMMET SIZE TO FIT CABLE O.D.	DIA. "D"	KIT P/N	NO. OF CONTACTS
W3280-1XPG-518(W)	0.18 - 0.20 [4.6-5.1mm]	Ø 0.77 [19.6mm]	W3280-10PG-5XX	(10) - #20
W3280-1XPG-521(W)	0.21 - 0.23 [5.3-5.8mm]	Ø 0.77 [19.6mm]	W3280-11PG-5XX	(11) - #20
W3280-1XPG-524(W)	0.24 - 0.27 [6.1-6.8mm]	Ø 0.77 [19.6mm]	W3280-12PG-5XX	(12) - #20
W3280-1XPG-528(W)	0.28 - 0.29 [7.1-7.4mm]	Ø 0.77 [19.6mm]	W3280-10PG-5XXW	(10) - #20
W3280-1XPG-530(W)	0.30 - 0.32 [7.6-8.1mm]	Ø 0.77 [19.6mm]	W3280-11PG-5XXW	(11) - #20
W3280-1XPG-535(W)	0.35 - 0.40 [8.9-10.2mm]	Ø 0.83 [21.1mm]	W3280-12PG-5XXW	(12) - #20
(WING COUPLING RING OPTION)				ADD W SUFFIX FOR WINGED COUPLING RING OPTION
NO. OF CONTACTS				W3280-1XPG-5XX(W)

GROMMET SIZE
SEE P/N LIST
NO. OF CONTACTS



CONTACT
INSERTION VIEW

#4 HI/LO SCREW
MAT'L: STAINLESS STEEL

BACKSHELL STRAP
MAT'L: UV THERMOPLASTIC,
BLACK



COUPLING RING
MAT'L: UV THERMOPLASTIC,
BLACK

COUPLING RING, WINGED (OPTIONAL)
MAT'L: UV THERMOPLASTIC,
BLACK

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

A	PAK	08/15/19	DRAWING CREATED & RELEASED PER DOR 10-2523JS-1	
REV.	INIT.	DATE	DESCRIPTION	
	PAK	10/01/14	ORIG. DRAWN BY: DATE: 10/01/14	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:	
UNLESS OTHERWISE SPECIFIED TOLERANCES 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE NTS	SIZE B
△ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SHEET 1 OF 1	
			FILE: W3280-1XPG-5XX	DIRECTORY: SLW
			TITLE: CABLE CONNECTOR KIT #20 PIN CONTACTS (CRIMP), BACKSHELL CLAMP MULTI-CON-X, E-KEY, WEATHER RESISTANT STANDARD PRODUCT	
			PART NUMBER: W3280-1XPG-5XX(W)	REV A