

## Han 10HPR-cover-CL- cord

	Part number	09 40 010 5483
	Specification	Han 10HPR-cover-CL- cord

### Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings With fixing cord

### Version

Size	10 B
Locking type	Central locking lever (on the hood)

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	257 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140192065
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors