

## Han 3HPR Hood cover,toggle lock,powder c



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 09 40 703 5403                                                                        |
| Specification      | Han 3HPR Hood cover,toggle lock,powder c                                              |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09407035403">https://b2b.harting.com/09407035403</a> |

### Identification

|                              |                      |
|------------------------------|----------------------|
| Category                     | Accessories          |
| Series of hoods/housings     | Han <sup>®</sup> HPR |
| Type of accessory            | Protection cover     |
| Description of the accessory | for hoods            |

### Version

|              |                |
|--------------|----------------|
| Size         | 3 A            |
| Locking type | Toggle locking |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65<br>IP68    |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12   |

### Material properties

|                         |                      |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast        |
| Surface (hood/housing)  | Powder-coated        |
| Colour (hood/housing)   | RAL 9005 (jet black) |
| Material (seal)         | NBR                  |
| RoHS                    | compliant            |
| ELV status              | compliant            |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Yes           |
| California Proposition 65 substances | Lead          |
|                                      | Nickel        |
|                                      | Naphthalene   |

## Specifications and approvals

|           |                                   |
|-----------|-----------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076             |
|           | CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | DNV GL                            |

## Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 10                                     |
| Net weight                     | 41.14 g                                |
| Country of origin              | China                                  |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140191914                          |
| ETIM                           | EC002314                               |
| eCl@ss                         | 27440208 Cap for industrial connectors |