




- NOTES:
- PARTS TO BE BULK PACKED.
 - SOLDER CONTACTS ARE PRESSED INTO CONNECTOR.
ALL SOLDER CUPS ARE TO BE FACING TOP KEY.
 - ALL DIMENSIONS ARE REFERENCE ONLY
DIMENSIONS IN BRACKETS [] ARE METRIC.




ASSEMBLED VIEW SHOWN
WITH STANDARD COUPLING RING




ASSEMBLED VIEW SHOWN
WITH WINGED COUPLING RING






FACE VIEW
W3282-12SG-5XX(W)




CABLE INSERT, FEMALE
MAT'L: UV THERMOPLASTIC,
BLACK




#20 SOCKET CONTACTS
SOLDER CUP,
GOLD PLATED
SEE NOTE 2




GROMMET,
MAT'L: RUBBER,
BLACK
FOR CABLE O.D.
SEE TABLE




SLEEVE
MAT'L: THERMOPLASTIC,
BLACK




BACKSHELL
MAT'L: UV THERMOPLASTIC,
BLACK




FACE VIEW
W3282-10SG-5XX(W)



FACE VIEW
W3282-11SG-5XX(W)



ASSEMBLED VIEW SHOWN
WITH STANDARD
COUPLING RING



ASSEMBLED VIEW SHOWN
WITH WINGED
COUPLING RING

KIT PART NO.	GROMMET SIZE TO FIT CABLE O.D.	DIA. "D"
W3282-1XSG-518(W)	0.18 - 0.20 [4.6-5.1mm]	Ø0.77 [19.6mm]
W3282-1XSG-521(W)	0.21 - 0.23 [5.3-5.8mm]	Ø0.77 [19.6mm]
W3282-1XSG-524(W)	0.24 - 0.27 [6.1-6.8mm]	Ø0.77 [19.6mm]
W3282-1XSG-528(W)	0.28 - 0.29 [7.1-7.4mm]	Ø0.77 [19.6mm]
W3282-1XSG-530(W)	0.30 - 0.32 [7.6-8.1mm]	Ø0.77 [19.6mm]
W3282-1XSG-535(W)	0.35 - 0.40 [8.9-10.2mm]	Ø0.83 [21.1mm]

(WINGED COUPLING RING OPTION)
NO. OF CONTACTS


#4 HI/LO SCREW
MAT'L: STAINLESS STEEL

BACKSHELL STRAP
MAT'L: UV THERMOPLASTIC,
BLACK



KIT P/N	NO. OF CONTACTS
W3282-10SG-5XX	(10) - #20
W3282-11SG-5XX	(11) - #20
W3282-12SG-5XX	(12) - #20
W3282-10SG-5XXW	(10) - #20
W3282-11SG-5XXW	(11) - #20
W3282-12SG-5XXW	(12) - #20
ADD W SUFFIX FOR WINGED COUPLING RING OPTION	
W3282-1XSG-5XX(W)	

GROMMET SIZE
SEE P/N LIST
NO. OF CONTACTS



WIRE VIEW

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL
INFORMATION PROPRIETARY TO CONXALL
CORPORATION. ANY REPRODUCTION,
DISCLOSURE, OR USE OF THIS
DOCUMENT /INFORMATION IS EXPRESSLY
PROHIBITED UNLESS AUTHORIZED IN
WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A	PAK	08/15/19	DRAWING CREATED & RELEASED PER DOR 10-2523JS-1	
REV.	INIT.	DATE	DESCRIPTION	
	PAK	10/01/14	ORIG. DRAWN BY: DATE: 10/01/14	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY: _____	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY: _____	
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE NTS	SHEET 1 OF 1
▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			FILE: W3282-1XSG-5XX	DIRECTORY: SLW
			TITLE: CABLE CONNECTOR KIT #20 SOCKET CONTACTS (SOLDER), BACKSHELL CLAMP MULTI-CON-X, E-KEY, WEATHER RESISTANT CUSTOMER: STANDARD PRODUCT	
			PART NUMBER: W3282-1XSG-5XX(W)	REV A