



| LOC | DIST | REVISIONS |     |                           |         |      |
|-----|------|-----------|-----|---------------------------|---------|------|
| AF  | 50   | P         | LTR | DESCRIPTION               | DATE    | DWN  |
|     |      |           | E3  | REVISED PER ECR-08-015055 | 24JUN08 | HMR  |
|     |      |           | E4  | REVISED PER ECO-09-024606 | 04DEC09 | KK   |
|     |      |           |     |                           |         | APVD |
|     |      |           |     |                           |         | GJ   |
|     |      |           |     |                           |         | AEG  |

- 1 SPECIFICATIONS:  
MAGNET WIRE; #21-#24 AWG  
0.51-0.79mm [.020-.029] DIA COPPER.  
UP TO 2 WIRES OF THE SAME  
SIZE MAY BE CONNECTED BY  
A SINGLE TERMINAL.
- 2 POCKET RECOMMENDATION: #1601424
- 3 POST TIN PLATED 5 MICRONS [.000200] MIN OVER  
NICKEL UNDERPLATE 1.25 MICRONS [.000050] MIN.
- 4 POST TIN-LEAD PLATE 5 MICRONS [.000200] MIN  
OVER COPPER UNDERPLATE 2.5 MICRONS [.000100] MIN
- 5 TERMINAL APPLICATION TO COMPLY WITH TYCO  
ELECTRONICS SPECIFICATION 114-13166 FIGURE 5.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING  
PER D.RENAUD/D.SINISI



|                           |            |          |             |
|---------------------------|------------|----------|-------------|
|                           |            | 3        | 4-1601038-3 |
|                           |            | 3        | 1601038-3   |
| SUPERSEDED BY 4-1601038-3 |            | 4        | 4-1601038-2 |
|                           | OBSOLETE   | 4        | 2-1601038-2 |
| SUPERSEDED BY 1601038-3   |            | 4        | 1601038-2   |
|                           | 6 OBSOLETE | UNPLATED | 1601038-1   |
|                           |            | FINISH   | PART NUMBER |

|                                        |  |                                      |                                                           |                 |                    |                         |
|----------------------------------------|--|--------------------------------------|-----------------------------------------------------------|-----------------|--------------------|-------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>MICHAEL S. FEHER<br>01MAR2002 | Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608 |                 |                    |                         |
| DIMENSIONS:<br>mm [INCHES]             |  | CHK<br>GENE JACONO<br>01MAR2002      | NAME                                                      |                 |                    |                         |
|                                        |  | APVD<br>GENE JACONO<br>01MAR2002     | PRODUCT SPEC                                              |                 |                    |                         |
|                                        |  |                                      | 108-2085                                                  |                 |                    |                         |
|                                        |  |                                      | APPLICATION SPEC                                          |                 |                    |                         |
| MATERIAL<br>BRASS<br>SPRING HARD       |  | FINISH<br>SEE TABLE                  | WEIGHT<br>-                                               | SIZE<br>A2      | CAGE CODE<br>00779 | DRAWING NO<br>C=1601038 |
| CUSTOMER DRAWING                       |  |                                      | SCALE<br>10:1                                             | SHEET<br>1 of 1 | REV<br>E4          | RESTRICTED TO<br>-      |