

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PREEPORT, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING
JS-223-B

JS-223-B

M

DRAWING
NUMBER

2

X

ISSUE

REPLACES

RELEASE NO. SR 10105

CHECK

REVISIONS

A 0021422
W E G
20 JUNE 66

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62

CHECK



21 FEB '62

CHECK

21 FEB '62

CHECK

21 FEB '62



NOTE -
1 - FURNISHED BULK PACKED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISM BASIC SWITCH INSTALLED		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE — — — — 1 OZ MAX		CONTACT ARRANGEMENT	BREAK DISTANCE	DO NOT SCALE PRINT	
RELEASE FORCE — — — — 4 GRAMS MIN				UNLESS OTHERWISE SPECIFIED	
DIFFERENTIAL TRAVEL — — — .030 MAX				DIMENSIONS ARE IN INCHES	
OVERTRAVEL — — — — — .030 MIN				TOLERANCES ARE:	
				ONE PLACE (.0) ± .030	
				TWO PLACE (.00) ± .015	
				THREE PLACE (.000) ± .005	
				ANGLES ±	
				WEIGHT	

0-50378