





NOTES:

1. METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
3. COLLARS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
4. JACK SCREWS: STEEL; NICKEL PLATED
5. CONNECTOR IS PART MARKED: 165X16949X CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH									
DO NOT ALTER CAD DRAWING BY HAND				tolerance ISO 2768-m		 dim. in mm	scale: 2:1 (5:1)		
							material: SEE NOTES		
								title: SCREEN CAP 50pos. for socket connector with jack screw	
a	Original					dwg no:		DIN-A3	
rev.	description	date	name			part no:		sh: 1	
					drawn	21.01.15	Herneboel	16K1A3574	
					appd.	21.01.15	Lehmenkühler	165X16949X	
					norm				
					d-old				