








THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LE313C0108	2013-12-16	Fisher	Change Plating and Package
D	CI91496	2019-08-29	NianPing Yu	Add UL Label
E	CI92063	2019-12-03	NianPing Yu	EXI



- Notes:
- * Important Dimension To Check.
 - * Housing: High temperature thermoplastic. UL94V-0, color is Natural white.
 - * Terminal: Copper Alloy, Gold Plated on contact area. Tin plated on solder tails.
 - * Solder Peg: Copper Alloy, Tin plated over Nickel.

UNIT: mm		TITLE SSL-1.1 DC JACK CONNECTOR 4-POS. W/O POST, SMT TYPE		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO SSL11-J4D00-000001	DRAWN BY NianPing Yu	DATE 2019-08-29
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 6:1	SIZE A4	SHEET 1 OF 2		DWG NO SSL11-J4D00-000001	CHECKED BY Fisher Wang	DATE 2019-08-29
REV. E		WC-REV. C.3	Inspection item			CUSTOMER ALTW	APPROVED BY Max Yang	DATE 2019-08-29



MATERIALS

- 1. Carrier Tape: Polystyren (PS)
 - 2. Cover Tape: Polystyren (PS)
 - 3. Reel: Polystyren (PS)
- QUANTITY
- 1. 1000Pcs Per Reel
 - 2. 8 Reel Per Carton (8000Pcs/Carton)
 - 3. Reference Standard: EIA-481-D
 - 4. Net Weight: 1.68Kg/Carton.
 - 5. Gross Weight: 5.8Kg/Carton.

UNIT:mm		TITLE		ITEM NO		DRAWN BY		DATE	
TOLERANCE		SSL-1.1 DC JACK CONNECTOR		SSL11-J4D00-000001		NianPing Yu		2019-08-29	
.X ±0.25		4-POS. W/O POST, SMT TYPE		DWG NO		CHECKED BY		DATE	
.XX ±0.1		SCALE 5:1		SSL11-J4D00-000001		Fisher Wang		2019-08-29	
.XXX ±0.05		SIZE A4		CUSTOMER		APPROVED BY		DATE	
ANGLES ±1°		SHEET 2 OF 2		ALTW		Max Yang		2019-08-29	
		REV. E							
		WC-REV. C.3							
		QC: Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.