

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .



COPYRIGHT



By

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	P1	CUTTING BURR DETAILS ADDED	07SEP2018	RK	PS

1. MATERIAL:
HOUSING: POLYAMIDE 6, UL94V-2.
COLOR: NATURAL (OFF WHITE).
TUBULAR CONTACT: BRASS, TIN PLATED.
SCREW: M3, STEEL, ZINC PLATED W/ NON-
HEXAVALENT CHROMATE (CHROME III).
WIRE PROTECTION: STAINLESS STEEL.
2. ELECTRICAL:
CURRENT RATING: 30A, 250V, 10-22 AWG.
CURRENT RATING: 25A, 250V, 12-24 AWG.
WIRE RANGE: 10-24 AWG.
3. ENVIRONMENTAL:
CONTINUOUS WORKING TEMP.: -35°C TO +100°C.
- 4 CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION
5. CUTTING BURR MAX. 1mm ALLOWED.



1776296-4 AS SHOWN

100.0	116.6	TSB500 1231DS	1-1776296-2
90.0	106.6	TSB500 1131DS	1-1776296-1
80.0	96.6	TSB500 1031DS	1-1776296-0
70.0	86.6	TSB500 0931DS	1776296-9
60.0	76.6	TSB500 0831DS	1776296-8
50.0	66.6	TSB500 0731DS	1776296-7
40.0	56.6	TSB500 0631DS	1776296-6
30.0	46.6	TSB500 0531DS	1776296-5
20.0	36.6	TSB500 0431DS	1776296-4
10.0	26.6	TSB500 0331DS	1776296-3
-	16.6	TSB500 0213DS	1776296-2
-	6.6	TSB500 0131DS	1776296-1
DIM B	DIM A	T & B PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 3/18/05	 TE Connectivity Ltd.	
DIMENSIONS: mm		CHK C RICHARD 3/18/05		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 3/18/05	NAME EUROPA TERMINAL BLOCK W/WIRE PROTECTOR MOUNTING HOLES DIA 3.1, 10mm PITCH	
		PRODUCT SPEC		
MATERIAL SEE NOTES		FINISH SEE NOTES	SIZE A3	
			CAGE CODE 000779	
			DRAWING NO C=1776296	
			RESTRICTED TO -	
			SCALE NTS	
			SHEET 1 OF 1	
			REV P1	