











PCB layout, component side



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200302.

0955 155 6612 333	2	4-40 UNC	Black insulator	Samples	
0955 155 3612 741	1			Reel packaging (140 connectors)	
0955 155 6612 741	2				
0955 155 7612 741	3				
0955 155 3611 741	1	M3			
0955 155 6611 741	2				
0955 155 7611 741	3				
Part number	PL	Nut			Index designation

	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.
	All rights reserved Department EL PD		Created by ZHUANGJ	Inspected by LUOK	Standardisation HOFFMANN	Sub.
	HARTING Electronics GmbH D-32339 Espelkamp		Title D-Sub str SMT 9-pole fem ass with screw nut & pin			Doc-Key / ECM-Nr. 100236647/UGD/001/C 500000139800
			Type TB	Number 0955155X61X		Rev. C Page 1/1