




OBSOLETE	LIGHT BLUE	AS SHOWN	5.21 [.205]	10.57 [.416]	13.18 [.519]	16.31 [.642]	8.38 [.330]	102312-5
	BLUE	AS SHOWN	5.21 [.205]	10.57 [.416]	13.18 [.519]	16.31 [.642]	8.38 [.330]	102312-4
	BLACK	PER DETAIL F	3.56 [.140] REF	8.26 [.325]	10.74 [.423]	13.36 [.526]	6.07 [.239]	3 102312-3
	BLACK	PER DETAIL F	3.56 [.140] REF	12.04 [.474]	14.53 [.572]	17.14 [.675]	9.86 [.388]	1 102312-2
	BLACK	AS SHOWN	5.21 [.205]	10.57 [.416]	13.18 [.519]	16.31 [.642]	8.38 [.330]	102312-1
	COLOR	HANDLE AREA	E	D	C	B	A	PART NUMBER

- 1 TO BE USED WITH AMP-LATCH™ CONNECTOR WITH STANDARD COVER.
- 2 MATING RECEPTACLE HEIGHT.
- 3 NOT RELEASED, NOT PRODUCTION TOOLED.
- 4 FLAME RETARDANT PBT. UL94V-0 RATED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
4

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± 1°
FINISH -

DWN
D.GELTZ
07/08/92

CHK
R.STONE
7-10-92

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

LATCH, UNIVERSAL HEADER, AMP-LATCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=102312

RESTRICTED TO
-

SCALE
10:1

SHEET
1 OF 1

REV
H1